

RA Mini SMP Female Connector Solder Attachment for FM-SR034CU-ST, .034 Semi-Rigid Cable



FMCN51270

Configuration

- Mini SMP Female Connector
- 50 Ohms
- Right Angle Body Geometry
- Connector Interface Types: FM-SR034CU-ST, .034 Semi-Rigid

Features

- Operating Frequency of 18 GHz Max.
- Excellent VSWR of 1.25:1
- Blind Mate Connector
- Gold over Nickel Plated Beryllium Copper Contact

Applications

- General Purpose Test
- Custom Cable Assemblies

Description

RA Mini SMP Female Standard Connector Solder Attachment for FM-SR034CU-ST and .034 Semi-Rigid Cable, part number FMCN51270, from Fairview Microwave is in-stock and ships same day. This Mini SMP female connector operates up to a maximum frequency of 18 GHz and offers excellent VSWR of 1.25:1. This blind mate connector is ideal for applications without direct visual or tactile access to the connection point, for example, when two circuit boards need to be mated. Its right angle body geometry facilitates connections in tight spaces.

Fairview's RA Mini SMP female connector FMCN51270 datasheet specifications and outline drawing are shown in this PDF below. Our extensive offering of RF, microwave and millimeter wave connectors allows designers to configure and customize their signal connections however they like. From providing an I/O for a board design to creating a custom cable assembly configuration, Fairview Microwave has a connector solution to meet your needs. Fairview Microwave also has the expertise to build your custom cable assemblies for you and ship them same-day.

Electrical Specifications

Description	Minimum	Typical	Maximum	Units
Frequency Range	DC		18	GHz
VSWR			1.25:1	
Insertion Loss			0.424	dB
Dielectric Withstanding Voltage (DC)			325	Vdc
Inner Conductor DC Resistance			6	mOhms
Outer Conductor DC Resistance			2	mOhms
Insulation Resistance	5,000			MOhms
Impedance		50		Ohms

Electrical Specification Notes:
Insertion loss is = $0.1 * \text{SQRT}(F(\text{GHz}))$ dB

Mechanical Specifications

Size

Length	0.155512 in [3.95 mm]
Width	0.155512 in [3.95 mm]
Height	0.25 in [6.35 mm]
Weight	0.015 lbs [6.8 g]
Engagement Force	3.5lbs [1.59kg]
Disengagement Force	5lbs [2.27kg]

RA Mini SMP Female Connector Solder Attachment
for FM-SR034CU-ST, .034 Semi-Rigid Cable



FMCN51270

Material Specifications

Description	Material	Plating
Contact	Beryllium Copper	Gold over Nickel
Insulation	Teflon	
Body	Beryllium Copper	Gold over Nickel

Mechanical Specification Notes:
Mating cycles: 1000 (smooth bore), 100 (full detent) minimum.

Environmental Specifications

Temperature	
Operating Range	-65 to +165 deg C
Thermal Shock	MIL-STD-202, Method 107, Condition B

Compliance Certifications (see [product page](#) for current document)

Plotted and Other Data

Notes:

RA Mini SMP Female Connector Solder Attachment for FM-SR034CU-ST, .034 Semi-Rigid Cable from Fairview Microwave is in-stock and available to ship same-day. All of our RF/microwave products are available off-the-shelf from our ISO 9001:2008 certified facilities in Lewisville, Texas. Fairview Microwave is RF on-demand.

For additional information on this product, please click the following link: [RA Mini SMP Female Connector Solder Attachment for FM-SR034CU-ST, .034 Semi-Rigid Cable FMCN51270](#)

URL: <https://www.fairviewmicrowave.com/mini-smp-female-fm-sr034cu-st-.034-semi-rigid-connector-fmcn51270-p.aspx>

The information contained within this document is accurate to the best of our knowledge and representative of the part described herein. It may be necessary to make modifications to the part and/or the documentation of the part in order to implement improvements. Fairview Microwave reserves the right to make such changes as required. Unless otherwise stated, all specifications are nominal. Fairview Microwave does not make any representation or warranty regarding the suitability of the part described herein for any particular purpose, and Fairview Microwave does not assume liability arising out of the use of any part or document.

FMCN51270 CAD Drawing

RA Mini SMP Female Connector Solder Attachment for FM-SR034CU-ST, .034 Semi-Rigid Cable

