

# 3 Way High Power Equal Tapper with 4.3-10 Operating from 600 MHz to 2.7 GHz Rated at 300 Watts

The FMDV1029 is a High Power Equal Power Tapper with 4.3-10 Female connectors rated to 300 watts CW. Insertion loss is a low 0.15 dB.

Fairview Microwave's family of Low PIM Equal Power Tappers (Tap Power Dividers) are designed without solder joints and a unique construction allows for exceptional performance within the 600 to 2,700 MHz frequency range. They are offered in a range of output port options to allow flexibility in the design of your DAS system. Especially designed and manufactured for the rigors of low PIM systems, this family of Tappers is rated at an average power of 300 watts CW, and have PIM performance of -160 dBc or better. They can be used indoor or outdoor as they meet the moisture requirements of IP67. They are available in four different connector types: N, DIN 7-16, 4.3-10, and Mini DIN 4.1/9.5.

### **Electrical Specifications**

Description	Min	Тур	Мах	Units	
Frequency Range	0.6		2.7	GHz	
Impedance		50		Ohms	
Insertion Loss			0.15	dB	
Passive Intermodulation 2 Tones @ 43 dBm: F1	= 1930 MHz, F2 =	= 1990	-160 D MHz	dBc	
Input Power (CW)			300	Watts	
Input Power (Peak)			3	KWatts	



FMDV1029 DATA SHEET

## **Features:**

- Low PIM (-160 dBc)
  - High Power 300 watt CW Rating
  - 600 to 2,700 MHz
  - 4.3-10 Female Connector
  - Mounting Bracket

## **Applications:**

- Indoor/Outdoor Use (IP67)
- Base Station
- 4G/LTE/AWS/PCS/PMR/ UMTS/TETRA/WiFi
- Distributed Antenna Systems (DAS)
- Wireless Infrastructure

## Specifications by Frequency

Description	F1	F2	F3	5 F4	F5	Unit	ts
Frequency Range	0.6-0. <mark>698</mark>	0.698-2.7				GHz	Z
Input VSWR, Max	1.3:1	1.15:1					

#### **Mechanical Specifications**

Weight	1.0642 lbs [482.71 g]
Housing Material and Plating	Aluminum, Chem Film
<b>Configuration</b> Package Type Input Connector Output Connector	Connectorized 4.3-10 Female 4.3-10 Female
Environmental Specifications Ingress Protection (IP) Rating	IP67

Fairview Microwave 1130 Junction Dr. #100 Allen, TX 75013 Tel: 1-800-715-4396 / (972) 649-6678 Fax: (972) 649-6689 www.fairviewmicrowave.com sales@fairviewmicrowave.com






## Compliance Certifications (see product page for current document)

#### **Plotted and Other Data**

Notes:

#### **Typical Performance Data**








3 Way High Power Equal Tapper with 4.3-10 Operating from 600 MHz to 2.7 GHz Rated at 300 Watts from Fairview Microwave is in-stock and available to ship same-day. All of our RF/microwave products are available off-the-shelf from our ISO 9001:2008 certified facilities in Allen, Texas. Fairview Microwave is RF on-demand.


For additional information on this product, please click the following link: 3 Way High Power Equal Tapper with 4.3-10 Operating from 600 MHz to 2.7 GHz Rated at 300 Watts FMDV1029

URL: https://www.fairviewmicrowave.com/3-way-equal-tapper-4.3-10-600-mhz-2.7-ghz-300watts-fmdv1029-p.aspx














FMDV1029 DATA SHEET

TOLERANCES: HOLE TOLERANCE: X.XXX ±.003 LENGTH TOLERANCE: X.XXX ±.010 LENGTH TOLERANCE: X.XX ±.03

FAIRVIEW MICROWAVE INC. ALLEN, TX 75013 WWW.FAIRVIEWMICROWAVE.COM	NOTES: 1. UNLESS OTHERWISE SPECIFIED ALL DIMENSIONS ARE NOMINAL. 2. ALL SPECIFICATIONS ARE SUBJECT TO CHANGE WITHOUT NOTICE AT ANY TIME. 3. DIMENSIONS ARE IN INCHES [mm].					
TITLE 3 Way High Power Equal Tapper with 4.3-10 Operating from 600 MHz to 2.7 GHz Rated at 300 Watts	DWG NO FMDV1029			CAGE CODE 3FKR5		
	CAD FILE 081816	SHEET	SCAL	E N/A	SIZE A	2233