

# FMWSP1008 DATA SHEET

## WR-90 Waveguide Pressurizing Section 4.25 Inch Length With CPR-90G Grooved Flange from 8.2 GHz to 12.4 GHz

The FMWSP1008 is a pressurizing section for WR-90 waveguides with CPR-90 Grooved flanges. The pressure section has a pressure gauge to monitor the internal pressure. The pressure gauge will read up to 15 PSI. It also has a pressure inlet valve which is a Schrader 1/8-27 NPTF with protective metal cap. The FMWSP1008 is part of a family of pressure inlets with pressure gauges. Used with Fairview Microwave's gasket kits it allows for waveguide systems to be pressurized with air or other gasses. These are quality built units with VSWR of 1.08:1 or less.



Description	Min	Тур	Max	Units
Frequency Range	8.2		12.4	GHz
VSWR		1.07:1		

<sup>\*</sup> Values at 25°C, sea level

## **Mechanical Specifications**

Waveguide Size WR-90 Waveguide Design Standard

Section Length 4.25 in [107.95 mm]

Flange 1

Flange Type CPR-90G Flange Designation None

### Waveguide

Interface WR-90 Material Bronze

Flange 2

Flange Type CPR-90G Flange Designation None

## **Compliance Certifications** (see product page for current document)

#### **Plotted and Other Data**

Notes:

Values at 25 °C, sea level



### Features:

- Pressurizing Waveguide Section
- 0-15 PSI Pressure Gauge
- 8.2 GHz to 12.4 GHz Frequency Range
- CPR-90 Grooved Flange
- Waveguide Body made of Bronze with Brass Flanges
- Low VSWR


Fairview Microwave 1130 Junction Dr. #100 Allen, TX 75013 Tel: 1-800-715-4396 / (972) 649-6678


Fax: (972) 649-6689 www.fairviewmicrowave.com sales@fairviewmicrowave.com





## **Typical Performance Data**





WR-90 Waveguide Pressurizing Section 4.25 Inch Length With CPR-90G Grooved Flange from 8.2 GHz to 12.4 GHz from Fairview Microwave is in-stock and available to ship same-day. All of our RF/microwave products are available off-the-shelf from our ISO 9001:2008 certified facilities in Allen, Texas. Fairview Microwave is RF on-demand.


For additional information on this product, please click the following link: WR-90 Waveguide Pressurizing Section 4.25 Inch Length With CPR-90G Grooved Flange from 8.2 GHz to 12.4 GHz FMWSP1008

URL: https://www.fairviewmicrowave.com/wr-90-waveguide-section-straight-cpr-90g-grooved-standard-fmwsp1008-p. aspx

The information contained in this document is accurate to the best of our knowledge and representative of the part described herein. It may be necessary to make modifications to the part and/or the documentation of the part, in order to implement improvements. Fairview Microwave reserves the right to make such changes as required. Unless otherwise stated, all specifications are nominal. Fairview Microwave does not make any representation or warranty regarding the suitability of the part described herein for any particular purpose, and Fairview Microwave does not assume any liability arising out of the use of any part or documentation.







FAIRVIEW MICROWAVE INC. NUIES:
1. UNLESS OTHERWISE SPECIFIED ALL DIMENSIONS ARE NOMINAL.
2. ALL SPECIFICATIONS ARE SUBJECT TO CHANGE WITHOUT NOTICE AT ANY TIME.
3. DIMENSIONS ARE IN INCHES [mm]. ALLEN, TX 75013 WWW.FAIRVIEWMICROWAVE.COM TITLE DWG NO CAGE CODE FMWSP1008 3FKR5 WR-90 Waveguide Pressurizing Section 4.25 Inch Length With CPR-90G Grooved Flange from 8.2 GHz to CAD FILE 062117 SHEET 1 OF 1 SCALE N/A SIZE A 9999 12.4 GHz