

# MC053SA-10 DATA SHEET

# SMA Directional Coupler 10 dB 3 GHz Rated To 50 Watts

Directional couplers are indispensable components for isolating, separating and combining signals. For example, they provide a simple way of sampling microwave signals. They also can make accurate attenuator measurements since reflections are eliminated. The MC053SA-10 is a 10 dB directional coupler that operates from 0.5 to 3 GHz and can handle up to 50 Watts (CW) with 18 dB directivity minimum and 1.3:1 VSWR maximum. The package interface uses SMA female connectors, and is also REACH and RoHS compliant.

The MC053SA-10 is part of Fairview Microwave's family of directional/dualdirectional couplers that offer coupling ratios up to 50 dB with excellent performance featuring high directivity, low insertion loss and VSWR. They are available in both narrow and broad bandwidths and can be used in a wide variety of applications including signal sampling, VSWR measurements, power combining and distribution.

#### **Electrical Specifications**

Description	Min	Ту	уp	Max	Units
Frequency Range	0.5			3	GHz
Impedance		5	0		Ohms
Coupling	10 ±1.5		dB		
Insertion Loss				1	dB
Directivity	18				dB
Main Line VSWR				1.3:1	
Sec. Line VSWR				1.3:1	
Input Power (CW)				50	Watts

Connectorized SMA Female SMA Female SMA Female

Electrical Specification Notes: Values at 25°C, sea level.

#### Mechanical Specifications

4.724 in [119.99 mm]
0.402 in [10.21 mm]
1.181 in [30 mm]
0.241 lbs [109.32 g]
Aluminum

#### Configuration

Package Type	
Input Connector	
Output Connector	
Coupled Connectors	

#### **Environmental Specifications**

Temp	erature
------	---------

Operating Range	-30 to +85 deg C



### **Features:**

- Directional Coupler
- 0.5 to 3 GHz Frequency Range
- Coupling 10±1.5 dB
- Directivity > 18 dB
- VSWR < 1.3:1
- Max Power 50 Watts (CW)

## **Applications:**

- Test and Measurement
- Military Communications
- Commercial Communications
- Wireless Communications
- SATCOM

Fairview Microwave 301 Leora Ln., Suite 100 Lewisville, TX 75056 Tel: 1-800-715-4396 / (972) 649-6678 Fax: (972) 649-6689 www.fairviewmicrowave.com sales@fairviewmicrowave.com





#### **Compliance Certifications** (see product page for current document)

#### **Plotted and Other Data**


Notes:

SMA Directional Coupler 10 dB 3 GHz Rated To 50 Watts from Fairview Microwave is in-stock and available to ship same-day. All of our RF/microwave products are available off-the-shelf from our ISO 9001:2008 certified facilities in Lewisville, Texas. Fairview Microwave is RF on-demand.


For additional information on this product, please click the following link: SMA Directional Coupler 10 dB 3 GHz Rated To 50 Watts MC053SA-10

URL: https://www.fairviewmicrowave.com/sma-directional-standard-10-db-3-ghz-mc053sa-10-p.aspx

The information contained in this document is accurate to the best of our knowledge and representative of the part described herein. It may be necessary to make modifications to the part and/or the documentation of the part, in order to implement improvements. Fairview Microwave reserves the right to make such changes as required. Unless otherwise stated, all specifications are nominal. Fairview Microwave does not make any representation or warranty regarding the suitability of the part described herein for any particular purpose, and Fairview Microwave does not assume any liability arising out of the use of any part or documentation.







MC053SA-10 DATA SHEET

301 Leora Ln., Suite 100, Lewisville, TX 75056 | Tel: 1-800-715-4396 / (972) 649-6678 / Fax: (972) 649-6689