

SMA/F POWER DIVIDER 2-WAY 7-12.4 GHZ

MP0712-2

SPECIFICATIONS

ELECTRICAL:

FREQUENCY: 7-12 GHZ
 VSWR 1.35:1 MAX
 INPUT POWER: 10 WATTS MAX
 ISOLATION: 20 DB MIN
 INSERTION LOSS: .4 DB
 IMPEDANCE: 50 OHMS


CONNECTORS:

NICKEL PLATED BRASS
 CONTACTS BeCu
 CONTACT PLATING: Au per MIL-G-45204


ENVIRONMENTAL:

TEMP: -55°C TO +125°C

ROHS COMPLIANT



MEASUREMENTS BELOW ARE TYPICAL



ALL DIMENSIONS IN inches(MM) Typical

FAIRVIEW MICROWAVE INC.

ALLEN, TX 75013 WWW.FAIRVIEWMICROWAVE.COM

TITLE

SMA/F POWER DIVIDER 2-WAY 7-12.4 GHZ

SIZE	CAGE CODE	DWG NO	REV
A	3FKR5	MP0712-2	A
SCALE	SHEET		