

SMA POWER DIVIDER 2-WAY 1-2 GHZ

MP8412-2

SPECIFICATIONS

ELECTRICAL:


FREQUENCY: 1-2 GHZ
 VSWR 1.20:1 MAX IN, 1.15 OUT
 POWER HANDLING: 30 WATTS

ISOLATION: 20 DB MIN
 INSERTION LOSS: 0.35 DB
 AMPLITUDE BALANCE: +/- 0.20 DB MAX
 PHASE BALANCE: +/- 2 DEGREES
 IMPEDANCE: 50 OHMS


ENVIRONMENTAL:

TEMP: -55 C TO +85 C

ROHS COMPLIANT



MEASUREMENTS BELOW ARE TYPICAL



ALL DIMENSIONS IN inches(MM) Typical

FAIRVIEW MICROWAVE INC.

ALLEN, TX 75013 WWW.FAIRVIEWMICROWAVE.COM

TITLE

SMA POWER DIVIDER 2-WAY 1-2 GHZ

SIZE	CAGE CODE	DWG NO	REV
A	3FKR5	MP8412-2	A
SCALE		SHEET	