

SMA POWER DIVIDER 4-WAY 0-3 GHZ

MPR03-04

SPECIFICATIONS


ELECTRICAL:

RESISTIVE POWER DIVIDER
 FREQUENCY: 0-3 GHZ
 VSWR 1.3:1 MAX
 POWER CW: 1 WATT
 INSERTION LOSS: 13 DB MAX
 IMPEDANCE: 50 OHMS


MATERIALS BODY: PASS STAINLESS STEEL

ENVIRONMENTAL:

OP TEMP: 0 TO +70 DEG C
 STORAGE TEMP: -55 C TO +120 C



MEASUREMENTS BELOW ARE TYPICAL



ALL DIMENSIONS IN inches(MM) Typical

FAIRVIEW MICROWAVE INC.

ALLEN, TX 75013 WWW.FAIRVIEWMICROWAVE.COM

TITLE

SMA POWER DIVIDER 4-WAY 0-3 GHZ

SIZE CAGE CODE DWG NO

A

3FKR5

MPR03-04

MPR03-04

REV

C

SCALE

SHEET