

0 to 101 dB Step Attenuator With a 1 dB Step BNC Female Connectors Rated Up To 1000 MHz and Up to 1 Watt in a Toggle Design

Electrical Specifications*

Description	Min	Typ	Max	Units
Frequency Range	DC		1,000	MHz
Impedance		50		Ohms
Attenuation Value		0 to 101		dB
Step Size		1		dB
Step Type		Toggle		
Input Power			1	Watts
VSWR			1.5:1	

* Values at 25°C, sea level

Mechanical Specifications

Size

Length	8.5 in [215.9 mm]
Width	1.75 in [44.45 mm]
Height	1.05 in [26.67 mm]
Weight	1.36201 lbs [617.8 g]

Connectors

Description	Connector 1	Connector 2
Type	BNC Female	BNC Female

Compliance Certifications (visit www.FairviewMicrowave.com for current document)

Plotted and Other Data

Notes:

- Values at 25 °C, sea level




Features:

- Design: Step, Bidirectional Attenuator
- Connector 1: BNC Female
- Connector 2: BNC Female
- Body Material and Plating: Aluminum

Fairview Microwave
 1130 Junction Dr. #100
 Allen, TX 75013
 Tel: 1-800-715-4396 / (972) 649-6678
 Fax: (972) 649-6689
www.fairviewmicrowave.com
sales@fairviewmicrowave.com

Typical Performance Data




0 to 101 dB Step Attenuator With a 1 dB Step BNC Female Connectors Rated Up To 1000 MHz and Up to 1 Watt in a Toggle Design from Fairview Microwave is in-stock and available to ship same-day. All of our RF/microwave products are available off-the-shelf from our ISO 9001:2008 certified facilities in Allen, Texas. Fairview Microwave is RF on-demand.

For additional information on this product, please click the following link: [0 to 101 dB Step Attenuator With a 1 dB Step BNC Female Connectors Rated Up To 1000 MHz and Up to 1 Watt in a Toggle Design SA1000](http://www.fairviewmicrowave.com/101db-step-attenuator-1db-bnc-female-dc-1000-mhz-1-watt-sa1000-p.aspx)

URL: <http://www.fairviewmicrowave.com/101db-step-attenuator-1db-bnc-female-dc-1000-mhz-1-watt-sa1000-p.aspx>

The information contained in this document is accurate to the best of our knowledge and representative of the part described herein. It may be necessary to make modifications to the part and/or the documentation of the part, in order to implement improvements. Fairview Microwave reserves the right to make such changes as required. Unless otherwise stated, all specifications are nominal. Fairview Microwave does not make any representation or warranty regarding the suitability of the part described herein for any particular purpose, and Fairview Microwave does not assume any liability arising out of the use of any part or documentation.



FAIRVIEW MICROWAVE INC. ALLEN, TX 75013 WWW.FAIRVIEWMICROWAVE.COM		NOTES: 1. UNLESS OTHERWISE SPECIFIED ALL DIMENSIONS ARE NOMINAL. 2. ALL SPECIFICATIONS ARE SUBJECT TO CHANGE WITHOUT NOTICE AT ANY TIME. 3. DIMENSIONS ARE IN INCHES [mm].			
TITLE 0 to 101 dB Step Attenuator With a 1 dB Step BNC Female Connectors Rated Up To 1000 MHz and Up to 1 Watt in a Toggle Design		DWG NO SA1000		CAGE CODE 3FKR5	
		CAD FILE 011415	SHEET	SCALE N/A	SIZE A