

7/16 DIN Male Connector Crimp/Non-Solder Contact Attachment For 0.240 inch, LMR-240, LMR-240-DB, LMR-240-UF, RG8X, B7808A Cable

7/16 DIN male connector with crimp/non-solder contact attachment for 0.240 inch, LMR-240, LMR-240-DB, LMR-240-UF, RG8X and B7808A, part number SC4945, from Fairview Microwave is in-stock and ships same day. This 7/16 DIN male connector operates up to a maximum frequency of 6 GHz and offers excellent VSWR of 1.25:1.

Fairview's 7/16 DIN male connector SC4945 datasheet specifications and outline drawing are shown in this PDF below. Our extensive offering of RF, microwave and millimeter wave connectors allows designers to configure and customize their signal connections however they like. From providing an I/O for a board design to creating a custom cable assembly configuration, Fairview Microwave has a connector solution to meet your needs. Fairview Microwave also has the expertise to build your custom cable assemblies for you and ship them same-day.

Electrical Specifications

Description	Min	Typ	Max	Units
Frequency Range	DC		6	GHz
VSWR			1.25:1	

Mechanical Specifications

Size	
Length	1.35 in [34.29 mm]
Weight	0.1905 lbs [86.41 g]

Material Specifications

Description	Material	Plating
Contact	Brass	Silver
Insulation	PTFE	
Body	Brass	Tri-Metal
Coupling Nut	Brass	Tri-Metal

Environmental Specifications

Compliance Certifications (see [product page](#) for current document)

Plotted and Other Data

Notes:



Configuration:

- 7/16 DIN Male Connector
- IEC 169-4
- 50 Ohms
- Straight Body Geometry
- 0.240 inch, LMR-240, LMR-240-DB, LMR-240-UF, RG8X, B7808A Interface Type
- Crimp/Non-Solder Contact Attachment

Features:

- Operating Frequency of 6 GHz Max.
- Excellent VSWR of 1.25:1
- Silver Plated Brass Contact

Applications:

- General Purpose Test
- Custom Cable Assemblies

Fairview Microwave
 1130 Junction Dr. #100
 Allen, TX 75013
 Tel: 1-800-715-4396 / (972) 649-6678
 Fax: (972) 649-6689
www.fairviewmicrowave.com
sales@fairviewmicrowave.com


7/16 DIN Male Connector Crimp/Non-Solder Contact Attachment For 0.240 inch, LMR-240, LMR-240-DB, LMR-240-UF, RG8X, B7808A Cable from Fairview Microwave is in-stock and available to ship same-day. All of our RF/microwave products are available off-the-shelf from our ISO 9001:2008 certified facilities in Allen, Texas. Fairview Microwave is RF on-demand.

For additional information on this product, please click the following link: [7/16 DIN Male Connector Crimp/Non-Solder Contact Attachment For 0.240 inch, LMR-240, LMR-240-DB, LMR-240-UF, RG8X, B7808A Cable SC4945](#)

URL: <https://www.fairviewmicrowave.com/7-16-male-standard-lmr-240-connector-sc4945-p.aspx>

The information contained in this document is accurate to the best of our knowledge and representative of the part described herein. It may be necessary to make modifications to the part and/or the documentation of the part, in order to implement improvements. Fairview Microwave reserves the right to make such changes as required. Unless otherwise stated, all specifications are nominal. Fairview Microwave does not make any representation or warranty regarding the suitability of the part described herein for any particular purpose, and Fairview Microwave does not assume any liability arising out of the use of any part or documentation.





STANDARD TOLERANCES	
.X	±0.2
.XX	±0.1
.XXX	±0.05

*STANDARD TOLERANCES APPLY ONLY TO DIMENSIONS IN INCHES

FAIRVIEW MICROWAVE INC. ALLEN, TX 75013 WWW.FAIRVIEWMICROWAVE.COM		NOTES: 1. UNLESS OTHERWISE SPECIFIED ALL DIMENSIONS ARE NOMINAL. 2. ALL SPECIFICATIONS ARE SUBJECT TO CHANGE WITHOUT NOTICE AT ANY TIME. 3. DIMENSIONS ARE IN INCHES [mm].			
TITLE 7/16 DIN Male Connector Crimp/Non-Solder Contact Attachment For 0.240 inch, LMR-240, LMR-240-DB, LMR-240-UF, RG8X, B7808A Cable		DWG NO SC4945		CAGE CODE 3FKR5	
CAD FILE	121316	SHEET	SCALE	N/A	SIZE A 41742