

SC6006 DATA SHEET

BNC Female Bulkhead Hermetically Sealed Connector Eyelet Terminal Solder Attachment IP 67 Rated

Configuration

Connector

BNC Female

Electrical Specifications*

Description	Min	Тур	Max	Units
Impedance		50		Ohms
AC DWV			1,500	Vrms

* Values at 25°C, sea level

Mechanical Specifications

Size

Length Width/Dia.

1.27 in [32.26 mm] 0.68 in [17.27 mm]

Connector

Type
Mating Cycles
Contact Material and Plating
Contact Plating Specification
Body Material and Plating
Body Plating Specification
Dielectric Type

BNC Female 500 Beryllium Copper, Gold 50µ in. minimum Beryllium Copper, Silver

200µ in. minimum

PTFE

Compliance Certifications (visit www.FairviewMicrowave.com for current

document)

RoHS Compliant

Yes

Plotted and Other Data

Notes:

Values at +25 °C, sea level

BNC Female Bulkhead Hermetically Sealed Connector Eyelet Terminal Solder Attachment IP 67 Rated from Fairview Microwave is in-stock and available to ship same-day. All of our RF/microwave products are available off-the-shelf from our ISO 9001:2008 certified facilities in Allen, Texas. Fairview Microwave is RF ondemand.

For additional information on this product, please click the following link: BNC Female Bulkhead Hermetically Sealed Connector Eyelet Terminal Solder Attachment IP 67 Rated SC6006

URL: http://www.fairviewmicrowave.com/bnc-female-standard-eyelet-terminal-connector-sc6006-p.aspx

The information contained in this document is accurate to the best of our knowledge and representative of the part described herein. It may be necessary to make modifications to the part and/or the documentation of the part, in order to implement improvements. Fairview Microwave reserves the right to make such changes as required. Unless otherwise stated, all specifications are nominal. Fairview Microwave does not make any representation or warranty regarding the suitability of the part described herein for any particular purpose, and Fairview Microwave does not assume any liability arising out of the use of any part or documentation.



Features:

• Specification: MIL-STD-348

Interface: Eyelet
Attachment: Solder
Body Style: Straight
Mount Method: Bulkhead
Iso. Ground/Hermetic:


Hermetically Sealed

Fairview Microwave 1130 Junction Dr. #100 Allen, TX 75013 Tel: 1-800-715-4396 / (972) 649-6678

Fax: (972) 649-6689 www.fairviewmicrowave.com sales@fairviewmicrowave.com







FAIRVIEW MICROWAVE INC. ALLEN, TX 75013 WWW.FAIRVIEWMICROWAVE.COM NOTES: 1. UNLESS OTHERWISE SPECIFIED ALL DIMENSIONS ARE NOMINAL. 2. ALL SPECIFICATIONS ARE SUBJECT TO CHANGE WITHOUT NOTICE AT ANY TIME. 3. DIMENSIONS ARE IN INCHES [mm].						
BNC Female Bulkhead Hermetically Sealed Connector	DWG NO SC6006			CAGE CODE 3FKR5		
Eyelet Terminal Solder Attachment IP 67 Rated	CAD FILE 081814	SHEET	SCALE	N/A	SIZE A	2233