

# SMA-F RG174, RG316 CRIMP CONN.

SC7077, SC7079

## SPECIFICATIONS

### ELECTRICAL:






FREQUENCY: 0-18 GHZ  
 VSWR 1.3:1 MAX  
 IMPEDANCE: 50 OHMS  
 OP. TEMP RANGE: -55C- +155C

### MECHANICAL:

MATERIAL BODY: PASSIVATED S STEEL  
 CENTER CONTACT: BeCu  
 CONTACT PLATING: Au MIL-G-45204  
 INSULATOR: TEFLON  
 INTERFACE: MIL-STD-348A

ROHS COMPLIANT

SC7077: Au PLATING  
 SC7079: PASSIVATED



STRIPPING DIMENSIONS

				<b>FAIRVIEW MICROWAVE INC.</b>	
				ALLEN, TX 75013 WWW.FAIRVIEWMICROWAVE.COM	
				TITLE	
				SMA-F RG174, RG316 CRIMP CONN.	
SIZE	CAGE CODE	DWG NO	REV		
A	3FKR5	SC7077, SC7079	A		
SCALE			SHEET		