

MCX-JACK RG178 CRIMP

SC9443

SPECIFICATIONS

ELECTRICAL:



FREQUENCY: 0-6 GHZ
VSWR 1.25:1 MAX
IMPEDANCE: 50 OHMS
OP. TEMP RANGE: -55C to +125C

MECHANICAL:

MATERIAL BODY: BRASS AU PLATING
CENTER CONTACT: BeCu
CONTACT PLATING: Au MIL-G-45204
CAPTIVATED CONTACT
INSULATOR: TEFLON
ROHS COMPLIANT

ASSEMBLY

TRIM CABLE AS SHOWN,
SLIDE CRIMP SLEEVE ON CABLE,
SOLDER ON CONTACT,
INSERT CABLE INTO BODY,
CRIMP



STRIPPING DIMENSIONS

FAIRVIEW MICROWAVE INC.

ALLEN, TX 75013 WWW.FAIRVIEWMICROWAVE.COM

TITLE

MCX-JACK RG178 CRIMP

SIZE	CAGE CODE	DWG NO	REV
A	3FKR5	SC9443	

SCALE

SHEET