

# BNC/M - BNC/M FLEXIBLE CABLES 1GHZ RG58

SCA23058-XX

## SPECIFICATIONS

### CABLE ASSEMBLY:

VSWR: 1.2:1 MAX @ < 1GHZ TYPICAL

### RAW CABLE: RG58DS

TYPICAL LOSS (EXCLUDING CONNECTORS)

@1GHZ: 0.15 DB/FT

@2GHZ: 0.22 DB/FT

@3GHZ: 0.28 DB/FT

OUTER SHIELD DIAMETER: .195"

### CONNECTORS:


BNC: BRASS

CONTACTS Au PLATING


INTERFACE: MIL-STD-348A

OP TEMP: -55-110°C

XX" +/- 0.100"



MEASUREMENTS BELOW ARE TYPICAL 12in CABLE



ALL DIMENSIONS IN inches(MM) Typical

**FAIRVIEW MICROWAVE INC.**

ALLEN, TX 75013 WWW.FAIRVIEWMICROWAVE.COM

TITLE

BNC/M - BNC/M FLEXIBLE CABLES 1GHZ RG58

SIZE	CAGE CODE	DWG NO	REV
A	3FKR5	SCA23058-XX	--
SCALE		SHEET	