

# BNC/M - BNC/M FLEXIBLE CABLES 6GHZ RG142

## SCA23142-XX SPECIFICATIONS


CABLE ASSEMBLY:  
VSWR:1.2:1 @ < 6GHZ TYPICAL

RAW CABLE: TIMES MICROWAVE RG142  
TYPICAL LOSS (EXCLUDING CONNECTORS)  
@100MHZ: 0.04 DB/FT  
@500MHZ: 0.09 DB/FT  
@1GHZ: 0.13 DB/FT  
@2GHZ: 0.19 DB/FT  
@3GHZ: 0.24 DB/FT  
OUTER SHIELD DIAMETER: .195"


CONNECTORS:  
BNC: BRASS  
CONTACTS Au PLATING  
INTERFACE: MIL-STD-348A

OP TEMP: -55-110°C

XX" +/- .100"



MEASUREMENTS BELOW ARE TYPICAL 12in CABLE



ALL DIMENSIONS IN inches(MM) Typical

**FAIRVIEW MICROWAVE INC.**

ALLEN, TX 75013 WWW.FAIRVIEWMICROWAVE.COM

TITLE

BNC/M - BNC/M FLEXIBLE CABLES 6GHZ RG142

SIZE

A

CAGE CODE

3FKR5

DWG NO

SCA23142-XX

REV

--

SCALE

SHEET