

SMA/M-SMA/F FLEXIBLE CABLE RG316

SCA42316-XX


SPECIFICATIONS

CABLE ASSEMBLY:
VSWR: 1.2:1 @ 3GHZ TYPICAL

RAW CABLE: RG316
TYPICAL LOSS (EXCLUDING CONNECTORS)
@100 MHZ: 0.08DB/FT
@1 GHZ: 0.26DB/FT
@2 GHZ: 0.38DB/FT
@3 GHZ: 0.47DB/FT

CONNECTORS:
BRASS
SMA torque 5-in-lbs
CONTACTS Au PLATING
INTERFACE: MIL-STD-348A

OP TEMP: -55 to +110°C



FAIRVIEW MICROWAVE INC.

ALLEN, TX 75013 WWW.FAIRVIEWMICROWAVE.COM

TITLE

SMA/M-SMA/F FLEXIBLE CABLE RG316

ALL DIMENSIONS IN inches(MM) Typical	SIZE A	CAGE CODE 3FKR5	DWG NO SCA42316-XX	REV --
	SCALE		SHEET	