

# SMA M/M FLEXIBLE CABLES LMR200 6GHZ

## SCA49200-XX

### SPECIFICATIONS


CABLE ASSEMBLY:  
VSWR: <1.2 TYPICAL @ 6 GHZ

RAW CABLE:  
LOSS (EXCLUDING CONNECTORS)  
@ 1GHZ: 0.10 DB/FT  
@ 2GHZ: 0.15 DB/FT  
@ 3GHZ: 0.19 DB/FT


OUTER DIAMETER: .200"

CONNECTORS:  
SMA: NICKEL PLATED BRASS  
CONTACTS: Au PLATING 30μ-in  
INTERFACE: MIL-STD-348A

TORQUE WRENCH: 5 IN-IBS



### MEASUREMENTS BELOW ARE TYPICAL



ALL DIMENSIONS IN inches(MM) Typical

## FAIRVIEW MICROWAVE INC.

ALLEN, TX 75013 WWW.FAIRVIEWMICROWAVE.COM

TITLE

SMA FLEXIBLE CABLES LMR200 6GHZ

SIZE	CAGE CODE	DWG NO	REV
A	3FKR5	SCA49200-XX	--
SCALE	SHEET		