

SCA52086-XX

SPECIFICATIONS


CABLE ASSEMBLY:
VSWR 1.25:1 MAX @ 18GHZ

RAW CABLE: (HUBER SUHNER MULTI.FLEX .086 OR EQ)
LOSS (EXCLUDING CONNECTORS)
@ 1GHZ: 0.23 DB/FT
@10GHZ: 0.8 DB/FT
@18GHZ: 1.1 DB/FT


OUTER SHIELD DIAMETER: .086"
OVERALL DIAMETER: .104"

CONNECTORS:
SMA: NICKEL PLATED BRASS
CONTACTS: Au PLATING 30 μ-IN
INTERFACE: MIL-STD-348A

TEMPERATURE RANGE: -55 to +110°C
TORQUE 5 IN-IBS



MEASUREMENTS BELOW ARE TYPICAL



ALL DIMENSIOS IN inches(MM) Typical

FAIRVIEW MICROWAVE INC.

ALLEN, TX 75013 WWW.FAIRVIEWMICROWAVE.COM

TITLE

SMA FLEXABLE CABLES 18GHZ 0.086"

SIZE A	CAGE CODE 3FKR5	DWG NO SCA52086-XX	REV A
SCALE		SHEET	