

SMP/F-SMA/M FLEXIBLE CABLES 18GHZ SF047

SCA63047-XX

SPECIFICATIONS

CABLE ASSEMBLY:

VSWR:1.35:1 @<18GHZ TYPICAL

RAW CABLE: HARVERHILL SF047

TYPICAL LOSS (EXCLUDING CONNECTORS)

@0.5GHz 0.28 dB/ft

@1GHz 0.399 dB/ft

@5GHz 0.899 dB/ft

@10GHz 1.302 dB/ft

@20GHz 1.899 dB/ft

CENTER CONDUCTOR DIAMETER: 0.0113"

OUTER SHIELD DIAMETER: .067"

CONNECTORS:

SMA: Nickel PLATED BRASS


CONTACTS Au PLATING

INTERFACE: MIL-STD-348A


SMP(GPOtm COMPATIBLE)

Au PLATED BeCu

ROHS COMPLIANT



MEASUREMENTS BELOW ARE TYPICAL



ALL DIMENSIONS IN inches(MM) Typical

FAIRVIEW MICROWAVE INC.

ALLEN, TX 75013 WWW.FAIRVIEWMICROWAVE.COM

TITLE

SMP/F-SMA/M FLEXIBLE CABLES 18GHZ SF047

SIZE

A

CAGE CODE

3FKR5

DWG NO

SCA63047-XX

REV

--

SCALE

SHEET