

# N/M - N/F FLEXIBLE CABLES 1GHZ RG58DS

SCB11974-XX

## SPECIFICATIONS

CABLE ASSEMBLY:

VSWR:1.2:1 @<1GHZ TYPICAL

RAW CABLE: RG58DS

TYPICAL LOSS (EXCLUDING CONNECTORS)

@1GHz: 0.15 DB/FT

@2GHz: 0.22 DB/FT


@3GHz: 0.28 DB/FT

CONNECTORS: BRASS


CONTACTS Au PLATING

INTERFACE: MIL-STD-348A

OP TEMP: -55-110°C



MEASUREMENTS BELOW ARE TYPICAL



ALL DIMENSIONS IN inches(MM) Typical

**FAIRVIEW MICROWAVE INC.**

ALLEN, TX 75013 WWW.FAIRVIEWMICROWAVE.COM

TITLE

N/M - N/F FLEXIBLE CABLES 1GHZ RG58DS

SIZE

**A**

CAGE CODE

3FKR5

DWG NO

**SCB11974-XX**

REV

--

SCALE

SHEET