

SCB15082-XX

SPECIFICATIONS


CABLE ASSEMBLY:
VSWR: <1.2 TYPICAL @ 2 GHZ

RAW CABLE:
LOSS (EXCLUDING CONNECTORS)
@ 1GHZ: 0.45 DB/FT
@2GHZ: 0.70 DB/FT


OVERALL DIAMETER: 0.080"

CONNECTORS:
SMA: NICKEL PLATED BRASS
CONTACTS: Au PLATING
INTERFACE: MIL-STD-348A

TORQUE WRENCH; 6 IN-IBS



MEASUREMENTS BELOW ARE TYPICAL



ALL DIMENSIONS IN inches(MM) Typical

FAIRVIEW MICROWAVE INC.

ALLEN, TX 75013 WWW.FAIRVIEWMICROWAVE.COM

TITLE

SMA FLEXIBLE CABLES RG178

SIZE	CAGE CODE	DWG NO	REV
A	3FKR5	SCB15082-XX	A
SCALE	SHEET		