

# SMA/M-SMA/F BULKHEAD FLEXIBLE CABLE RG174

SCB15208-XX


## SPECIFICATIONS

CABLE ASSEMBLY:  
VSWR: 1.2:1 @ < 12GHz TYPICAL


RAW CABLE: RG174  
TYPICAL LOSS (EXCLUDING CONNECTORS)  
@0.1GHz 0.08 DB/FT  
@0.5GHz 0.19 DB/FT  
@1GHz 0.27 DB/FT  
@2GHz 0.39 DB/FT  
@3GHz 0.49 DB/FT

CONNECTORS:  
BODY: BRASS  
SMA torque 5-in-lbs  
CONTACTS Au PLATING  
INTERFACE: MIL-STD-348A

TEMPERATURE: -55°C to +110°C



MEASUREMENTS BELOW ARE TYPICAL



ALL DIMENSIONS IN inches(MM) Typical

<b>FAIRVIEW MICROWAVE INC.</b>			
ALLEN, TX 75013 WWW.FAIRVIEWMICROWAVE.COM			
TITLE			
SMA/M-SMA/F BULKHEAD FLEXIBLE CABLE RG174			
SIZE	CAGE CODE	DWG NO	REV
<b>A</b>	3FKR5	<b>SCB15208-XX</b>	--
SCALE		SHEET	