

# SMA/MRA SMA/F/BKHD 2GHZ RG174 FLEXIBLE CABLES

## SCB15245-XX

### SPECIFICATIONS


CABLE ASSEMBLY:  
VSWR: <1.2 TYPICAL @ 2GHZ

RAW CABLE:  
LOSS (EXCLUDING CONNECTORS)  
@ 1GHZ: 0.27 DB/FT  
@ 2GHZ: 0.39 DB/FT  
@ 3GHZ: 0.49 DB/FT

OUTER DIAMETER: .011"


CONNECTORS:  
SMA: NICKEL PLATED BRASS  
INTERFACE: MIL-STD-348A  
CONTACTS; Au PLATTING

TORQUE 5 IN-IBS



\*\*XX - LENGTH OF CABLE IN INCHES

MEASUREMENTS BELOW ARE TYPICAL



ALL DIMENSIONS IN inches(MM) Typical

<b>FAIRVIEW MICROWAVE</b>			
FAIRVIEW, TX WWW.FAIRVIEWMICROWAVE.COM			
TITLE SMA/MRA SMA/F/BKHD 2GHZ RG174 FLEXIBLE CABLES			
SIZE <b>A</b>	CAGE CODE 3FKR5	DWG NO <b>SCB15245-XX</b>	REV --
SCALE		SHEET	