

SMA/M-BNC/M FLEXIBLE CABLES 1GHZ RG58

SCB15366-XX


SPECIFICATIONS

CABLE ASSEMBLY:
VSWR:1.2:1 @<1GHZ TYPICAL


RAW CABLE: RG58
TYPICAL LOSS (EXCLUDING CONNECTORS)
@1GHz: 0.15 DB/FT
@2GHz: 0.22 DB/FT
@3GHz: 0.28 DB/FT
@6GHz: 0.41 DB/FT

CONNECTORS:
BNC: BRASS
SMA torque 5-in-lbs
CONTACTS Au PLATING
INTERFACE: MIL-STD-348A

OP TEMP: -55-110°C
ROHS COMPLIANT



MEASUREMENTS BELOW ARE TYPICAL



ALL DIMENSIONS IN inches(MM) Typical

FAIRVIEW MICROWAVE INC.			
ALLEN, TX 75013 WWW.FAIRVIEWMICROWAVE.COM			
TITLE			
SMA/M-BNC/M FLEXIBLE CABLES 1GHZ RG58			
SIZE	CAGE CODE	DWG NO	REV
A	3FKR5	SCB15366-XX	--
SCALE		SHEET	