



SMA/M - BNC/M FLEXIBLE CABLES 1GHZ RG316

SCB15371-XX

SPECIFICATIONS

CABLE ASSEMBLY:

VSWR:1.5:1 @ < 1GHZ TYPICAL

RAW CABLE: RG316

TYPICAL LOSS (EXCLUDING CONNECTORS)

@ 100MHZ: 0.08 DB/FT

@ 1GHZ: 0.26 DB/FT

@ 2GHZ: 0.38 DB/FT

@ 3GHZ: 0.47 DB/FT

CONNECTORS:


BNC: BRASS

SMA torque 5-in-lbs


CONTACTS Au PLATING

INTERFACE: MIL-STD-348A

OP TEMP: -55-110°C



MEASUREMENTS BELOW ARE TYPICAL



ALL DIMENSIONS IN inches(MM) Typical

FAIRVIEW MICROWAVE INC.

ALLEN, TX 75013 WWW.FAIRVIEWMICROWAVE.COM

TITLE

SMA/M - BNC/M FLEXIBLE CABLES 1GHZ RG316

SIZE

A

CAGE CODE

3FKR5

DWG NO

SCB15371-XX

REV

--

SCALE

SHEET

