

N/M - N/M- FLEXIBLE CABLES 3GHZ LMR240

SCB15586-XX

SPECIFICATIONS

CABLE ASSEMBLY:

VSWR:1.2:1 @ < 3GHZ TYPICAL

RAW CABLE: LMR240

TYPICAL LOSS (EXCLUDING CONNECTORS)

@1GHz: 0.081 DB/FT

@2GHz: 0.116 DB/FT


@6GHz: 0.205 DB/FT

CONNECTORS: BRASS


CONTACTS Au PLATING 30 μ-in

INTERFACE: MIL-STD-348A

OP TEMP: -55-110°C



MEASUREMENTS BELOW ARE TYPICAL



ALL DIMENSIONS IN inches(MM) Typical

FAIRVIEW MICROWAVE INC.

ALLEN, TX 75013 WWW.FAIRVIEWMICROWAVE.COM

TITLE

N/M - N/M- FLEXIBLE CABLES 3GHZ LMR240

SIZE	CAGE CODE	DWG NO	REV
A	3FKR5	SCB15586-XX	--
SCALE			SHEET