



BNC/M - BNC/M FLEXIBLE CABLES 3GHZ RG316DS

SCB18181-XX

SPECIFICATIONS



CABLE ASSEMBLY:
VSWR:1.2:1 @3GHZ TYPICAL

RAW CABLE: RG316DS
TYPICAL LOSS (EXCLUDING CONNECTORS)
@100MHz: 0.08 DB/FT
@1GHz: 0.29 DB/FT
@3GHz 0.54 DB/FT

OUTER SHIELD DIAMETER: .195"

CONNECTORS:
BNC: BRASS
CONTACTS Au PLATING
INTERFACE: MIL-STD-348A
MAX OPERATING VOLTAGE(RMS): 900
OP TEMP: -55 to +110°C

XX" +/- .040"



ALL DIMENSIONS IN inches(MM) Typical

FAIRVIEW MICROWAVE INC.

ALLEN, TX 75013 WWW.FAIRVIEWMICROWAVE.COM

TITLE
BNC/M - BNC/M FLEXIBLE CABLES 3GHZ RG316DS

SIZE A	CAGE CODE 3FKR5	DWG NO SCB18181-XX	REV --
------------------	--------------------	------------------------------	-----------

SCALE	SHEET
-------	-------

