

SMA/M-MMCX/M FLEXIBLE CABLES RG316

SCB18840-XX

SPECIFICATIONS

CABLE ASSEMBLY:

VSWR:1.2:1 @< 3GHZ TYPICAL

RAW CABLE: RG316

TYPICAL LOSS (EXCLUDING CONNECTORS)

@ 100MHZ: 0.08 DB/FT

@1GHZ: 0.26 DB/FT

@2GHZ: 0.38 DB/FT

@3GHZ: 0.47 DB/FT

CONNECTORS: BRASS


SMA: torque 5-in-lbs

CONTACTS Au PLATING 30uin


INTERFACE: MIL-STD-348A

OP TEMP: -55-110°C

ROHS COMPLIANT



MEASUREMENTS BELOW ARE TYPICAL



ALL DIMENSIONS IN inches(MM) Typical

FAIRVIEW MICROWAVE INC.

ALLEN, TX 75013 WWW.FAIRVIEWMICROWAVE.COM

TITLE

SMA/M-MMCX/M FLEXIBLE CABLES RG316

SIZE CAGE CODE DWG NO

A

3FKR5

SCB18840-XX

REV

--

SCALE

SHEET