



TNC/M-TNC/F FLEXIBLE CABLES 1GHZ RG58

SCB19309-XX


SPECIFICATIONS

CABLE ASSEMBLY:
VSWR:1.2:1 @1GHZ TYPICAL

RAW CABLE: RG58
TYPICAL LOSS (EXCLUDING CONNECTORS)
@1GHz: 0.15 DB/FT

CONNECTORS:
BRASS
CONTACTS Au PLATING
INTERFACE: MIL-STD-348A

OP TEMP: -55-110°C
ROHS COMPLIANT



FAIRVIEW MICROWAVE INC.

ALLEN, TX 75013 WWW.FAIRVIEWMICROWAVE.COM

TITLE
TNC/M-TNC/F FLEXIBLE CABLES 1GHZ RG58

ALL DIMENSIONS IN inches(MM) Typical	SIZE	CAGE CODE	DWG NO	REV
	A	3FKR5	SCB19309-XX	--
	SCALE		SHEET	

