



2.4mm Female to 2.4mm Female 4 Hole Flange Adapter

2.4mm female to 2.4mm female 4 hole flange adapter part number SM3017 from Fairview Microwave is in-stock and ships same day. This Fairview 2.4mm to 2.4mm adapter has a female to female gender configuration. SM3017 2.4mm female to 2.4mm female adapter operates to 50 GHz. The Fairview Microwave RF adapter provides good VSWR of 1.3:1 maximum. The 2.4mm connector mates mechanically with commercially available 1.85mm (V) connectors. Our RF 2.4mm to 2.4mm 4 hole flange adapter allows designers to create external connections on their product enclosures, and can be used in a variety of other rack mount and panel mount applications.

RF adapters can be used to enable connections between two connector types that would otherwise not mate. Certain RF adapter configurations can also be used to protect connectors on expensive equipment where the number of connect and disconnect cycles is high. An RF, microwave, or millimeter wave adapter is connected to the equipment and the commonly changed connection is made with the adapter which can be easily replaced when it wears out after high usage; such adapters are referred to as connector savers. Fairview Microwave also offers bulkhead, panel mount, hermetically sealed, reverse polarity, and isolated ground adapter varieties to serve all of your RF, microwave and millimeter wave needs.

Electrical Specifications

Min	Тур	Max	Units
DC		50	GHz
		1.3:1	
		-76	DC 50

Mechanical Specifications

0.0175 lbs [7.94 g]
0.843 in [21.41 mm] 0.5 in [12.7 mm] 0.5 in [12.7 mm]
0.040 / 504 /4

Connector 1	Connector 2	
2.4mm Female	2.4mm Female	
Standard	Standard	
500	500	
	2.4mm Female Standard	2.4mm Female 2.4mm Female Standard Standard

Material Specifications

Description Connector 1		Connector 2				
Туре	2.4mm Female	2.4mm Female				
Contact Material	Beryllium Copper	Beryllium Copper				
Contact Plating	Gold over Nickel	Gold over Nickel				
Contact Plating Spec.	MIL-G-45204	MIL-G-45204				
Insulation Material	Oxide-Noryl	Oxide-Noryl				
Outer Contact Material	Passivated Stainless Steel	Passivated Stainless Steel				
Outer Contact Plating Spec.	ASTM A380	ASTM A380				



Configuration:

- 2.4mm Female Connector 1
- 2.4mm Female Connector 2
- 50 Ohm
- Straight Body Geometry
- 4 Hole Flange Mount Method

Features:

- VSWR of 1.3:1 max up to 50 GHz
- Contact plating according to MIL-G-45204
- Gold over Nickel Plated Beryllium Copper Contact

Applications:

- General Purpose Test
- Rack Mounted Equipment

Fairview Microwave 301 Leora Ln., Suite 100 Lewisville, TX 75056 Tel: 1-800-715-4396 / (972) 649-6678 Fax: (972) 649-6689 www.fairviewmicrowave.com

sales@fairviewmicrowave.com





Environmental Specifications

Temperature


Operating Range Vibration Salt Spray -55 to +100 deg C MIL-STD 202, Method 204, Condition D (20 G's) MIL-STD 202, Method 101, Condition B, 5% salt solution

Compliance Certifications (see product page for current document)

Plotted and Other Data

Notes:

Typical Performance Data



2.4mm Female to 2.4mm Female 4 Hole Flange Adapter from Fairview Microwave is in-stock and available to ship sameday. All of our RF/microwave products are available off-the-shelf from our ISO 9001:2008 certified facilities in Allen, Texas. Fairview Microwave is RF on-demand.


For additional information on this product, please click the following link: 2.4mm Female to 2.4mm Female 4 Hole Flange Adapter SM3017


URL: https://www.fairviewmicrowave.com/2.4mm-female-2.4mm-female-4-hole-flange-adapter-sm3017-p.aspx

The information contained in this document is accurate to the best of our knowledge and representative of the part described herein. It may be necessary to make modifications to the part and/or the documentation of the part, in order to implement improvements. Fairview Microwave reserves the right to make such changes as required. Unless otherwise stated, all specifications are nominal. Fairview Microwave does not make any representation or warranty regarding the suitability of the part described herein for any particular purpose, and Fairview Microwave does not assume any liability arising out of the use of any part or documentation.














STANDARD TOLERANCES

.X ±0.2 .XX ±0.01 .XXX ±0.005

*STANDARD TOLERANCES APPLY ONLY TO DIMENSIONS IN INCHES

Fairview Microwave President on Demand.	NOTES: 1. UNLESS OTHERWISE SPECIFIED ALL DIMENSIONS ARE NOMINAL. 2. ALL SPECIFICATIONS ARE SUBJECT TO CHANGE WITHOUT NOTICE AT ANY TIME. 3. DIMENSIONS ARE IN INCHES [mm].						
2.4mm Female to 2.4mm Female 4 Hole Flange Adapter	DWG NO SM3017				CAGE CODE 3FKR5		
	CAD FILE	05/09/18	SHEET	1 OF 1	SCAL	E N/A	SIZE A