

N/F-BNC/M FLANGE ADAPTER

SM3517

SPECIFICATIONS


ELECTRICAL

FREQUENCY: 0-4 GHz
IMPEDANCE: 50 OHMS
VSWR: 1.2:1 MAX

MECHANICAL


MATERIALS BODY: NICKLE PLATED BRASS
MATERIALS CONTACTS: BeCu, Si PLATING
INTERFACE: MIL-STD-348A
PLATING: MIL-G-45204

.627" MAX DIA
(15.90)



0.67"
(17.02)

1.47"
(37.34)




(4X) .125
(3.18)

.718"
(18.24)

1.000" SQ
(25.4)

MEASUREMENTS BELOW ARE TYPICAL



ALL DIMENSIONS IN inches(MM) Typical

FAIRVIEW MICROWAVE INC.

ALLEN, TX 75013 WWW.FAIRVIEWMICROWAVE.COM

TITLE

N/F-BNC/M FLANGE ADAPTER

SIZE

A

CAGE CODE

3FKR5

DWG NO

SM3517

REV

A

SCALE

SHEET