

# SMB-BNC ADAPTERS 4GHZ

SM3634

## SPECIFICATIONS

### ELECTRICAL

FREQUENCY: 0-4 GHZ

IMPEDANCE: 50 OHMS

VSWR: 1.2:1 MAX @ 2 GHZ

1.35:1 MAX @ 4 GHZ

### MECHANICAL

MATERIAL BODY: NICKEL PLATED BRASS


CONTACTS: BeCu

CONTACT PLATING: Au PER MIL-G-45204


INSULATOR: TEFLON

INTERFACE: MIL-STD-348A

TEMPERATURE: -65° +125°C



MEASUREMENTS BELOW ARE TYPICAL



ALL DIMENSIONS IN inches(MM) Typical

**FAIRVIEW MICROWAVE INC.**

ALLEN, TX 75013 WWW.FAIRVIEWMICROWAVE.COM

TITLE

**SMB-BNC ADAPTERS 4GHZ**

SIZE

**A**

CAGE CODE

3FKR5

DWG NO

SM3634

REV

**A**

SCALE

SHEET