

WR-62 Waveguide Section 6 Inch Length Straight Using UG-419/U Flange With a 12.4 GHz to 18 GHz Frequency Range in Standard

Electrical Specifications*

| Description | Min | Typ | Max | Units |
|-----------------|------|-----|------------|--------------|
| Frequency Range | 12.4 | | 18 | GHz |
| VSWR | | | 1.03:1 | |
| Insertion Loss | | | 0.1 [0.33] | dB/ft [dB/m] |

* Values at 25°C, sea level

Mechanical Specifications

Waveguide Size: WR-62
 Waveguide Design: Standard
 Section Length: 6 in [152.4 mm]

Flange 1

Interface: UG-419/U
 Material: Copper Alloy
 Plating: Paint

Waveguide

Interface: WR-62
 Material: Copper Alloy
 Plating: Paint

Flange 2

Interface: UG-419/U
 Material: Copper Alloy
 Plating: Paint

Compliance Certifications (visit www.FairviewMicrowave.com for current document)

Plotted and Other Data

Notes:
 • Values at 25 °C, sea level



Fairview Microwave
 1130 Junction Dr. #100
 Allen, TX 75013
 Tel: 1-800-715-4396 / (972) 649-6678
 Fax: (972) 649-6689
www.fairviewmicrowave.com
sales@fairviewmicrowave.com

WR-62 Waveguide Section 6 Inch Length Straight Using UG-419/U Flange With a 12.4 GHz to 18 GHz Frequency Range in Standard from Fairview Microwave is in-stock and available to ship same-day. All of our RF/microwave products are available off-the-shelf from our ISO 9001:2008 certified facilities in Allen, Texas. Fairview Microwave is RF on-demand.


For additional information on this product, please click the following link: [WR-62 Waveguide Section 6 Inch Length Straight Using UG-419/U Flange With a 12.4 GHz to 18 GHz Frequency Range in Standard SMF62S-06](#)

URL: <http://www.fairviewmicrowave.com/wr-62-waveguide-section-ug-419-flange-12.4-18-ghz-smf62s-06-p.aspx>

The information contained in this document is accurate to the best of our knowledge and representative of the part described herein. It may be necessary to make modifications to the part and/or the documentation of the part, in order to implement improvements. Fairview Microwave reserves the right to make such changes as required. Unless otherwise stated, all specifications are nominal. Fairview Microwave does not make any representation or warranty regarding the suitability of the part described herein for any particular purpose, and Fairview Microwave does not assume any liability arising out of the use of any part or documentation.



| WR62 | |
|-----------|--------|
| PN | Length |
| SMF62S-3 | 3 in. |
| SMF62S-6 | 6 in. |
| SMF62S-9 | 9 in. |
| SMF62S-12 | 12 in. |



| | | | | | |
|---|--------|---|-------|--------------------|-------------|
| FAIRVIEW MICROWAVE INC. ALLEN, TX 75013 WWW.FAIRVIEWMICROWAVE.COM | | NOTES: 1. UNLESS OTHERWISE SPECIFIED ALL DIMENSIONS ARE NOMINAL. 2. ALL SPECIFICATIONS ARE SUBJECT TO CHANGE WITHOUT NOTICE AT ANY TIME. 3. DIMENSIONS ARE IN INCHES [mm]. | | | |
| TITLE WR-62 Waveguide Section 6 Inch Length Straight Using UG-419/U Flange With a 12.4 GHz to 18 GHz Frequency Range in Standard | | DWG NO SMF62S | | CAGE CODE 3FKR5 | |
| CAD FILE | 062414 | SHEET | SCALE | N/A | SIZE A 2233 |