



# WR159 to N-F WAVEGUIDE TO COAXIAL ADAPTER

SMW159ACNG


## SPECIFICATIONS

FREQUENCY: 4.9-7.5 GHZ  
 VSWR: 1.25:1 MAX  
 MATERIAL BODY: AI  
 MATERIAL CONNECTORS:  
 BODY: NICKLE PLATED BRASS  
 CONTACTS: BeCu Au PLATED 30μ-in  
 CONN INTERFACE: MIL-STD-883  
 TEMPERATURE RANGE: -55° to 120°C

ROHS COMPLIANT



MEASUREMENTS BELOW ARE TYPICAL



ALL DIMENSIONS IN inches(MM) Typical

**FAIRVIEW MICROWAVE INC.**

ALLEN, TX 75013 WWW.FAIRVIEWMICROWAVE.COM

TITLE

**WR159 to N-F WAVEGUIDE TO COAXIAL ADAPTER**

SIZE

**A**

CAGE CODE

**3FKR5**

DWG NO

**SMW159ACNG**

REV

--

SCALE

SHEET