

4.3-10 Female Bulkhead Low PIM Connector Solder Attachment for TFT-5G-402



TC-402-4310F-BH-LP



Times Microwave Systems Connector Specification

Configuration

- 4.3-10 Female Connector
- 50 Ohms
- Straight Body Geometry
- Connector Interface Types: TFT-5G-402
- Bulkhead
- Low PIM Design

Features

- Operating Frequency of 6 GHz Max.
- Excellent VSWR of 1.25:1
- PIM levels better than -160 dBc
- Silver Plated Phosphor Bronze Contact
- 200 µin contact plating

Applications

- General Purpose Test
- Rack and Panel Mount Applications
- Wireless Communications
- Custom Cable Assemblies
- Low PIM Applications
- Distributed Antenna Systems (DAS)

Description

4.3-10 Female Bulkhead Low PIM Bulkhead Connector Solder/Solder Attachment for TFT-5G-402 Cable, part number TC-402-4310F-BH-LP, from Fairview Microwave is in-stock and ships same day. This 4.3-10 female connector operates up to a maximum frequency of 6 GHz and offers excellent VSWR of 1.25:1. The 4.3-10 female connector also has low passive intermodulation (PIM) of -160 dBc. Fairview's TC-402-4310F-BH-LP bulkhead 4.3-10 connector enables designers to make external connections on product enclosures, and can be used in a variety of other rack mount and panel mount applications.

Fairview's 4.3-10 female bulkhead connector TC-402-4310F-BH-LP datasheet specifications and outline drawing are shown in this PDF below. Our extensive offering of RF, microwave and millimeter wave connectors allows designers to configure and customize their signal connections however they like. From providing an I/O for a board design to creating a custom cable assembly configuration, Fairview Microwave has a connector solution to meet your needs. Fairview Microwave also has the expertise to build your custom cable assemblies for you and ship them same-day.

Electrical Specifications

| Description | Minimum | Typical | Maximum | Units |
|-------------------------|---------|---------|---------|-------|
| Frequency Range | DC | | 6 | GHz |
| VSWR | | | 1.25:1 | |
| Insertion Loss | | | 0.24 | dB |
| Passive Intermodulation | | | -160 | dBc |
| Operating Voltage (DC) | | | 2,500 | Vdc |
| Insulation Resistance | 5,000 | | | MOhms |
| Impedance | | 50 | | Ohms |

Performance by Frequency

| Description | F1 | F2 | F3 | F4 | F5 | Units |
|-----------------|---------|--------|----|----|----|-------|
| Frequency Range | DC to 3 | 3 to 6 | | | | GHz |
| VSWR, Max | 1.1:1 | 1.25:1 | | | | |

4.3-10 Female Bulkhead Low PIM Connector
Solder Attachment for TFT-5G-402



TC-402-4310F-BH-LP

Electrical Specification Notes:
Insertion Loss is 0.1*sqrt(FGHz)

Mechanical Specifications

| | |
|-----------------------|---------------------|
| Size | |
| Length | 1.449 in [36.8 mm] |
| Width | 0.867 in [22.02 mm] |
| Height | 0.867 in [22.02 mm] |
| Weight | 0.03 lbs [13.61 g] |
| Mating Cycles | 500 Cycles |
| Cable Retention Force | 22 lbs [9.98 kg] |

Material Specifications

| Description | Material | Plating |
|-----------------|-----------------|---------------------|
| Contact | Phosphor Bronze | Silver 200 µin |
| Insulation | PTFE | |
| Outer Conductor | Brass | Tri-Metal 80 µin |
| Body | Brass | Tri-Metal 80 µin |

Environmental Specifications

| | |
|--------------------|----------------------------------|
| Temperature | |
| Operating Range | -55 to +85 deg C |
| Shock | MIL-STD 202G, Meth. 213, Cond. I |
| Vibration | MIL-STD 202G, Meth. 204, Cond. B |
| Thermal Shock | MIL-STD 202G, Meth. 107, Cond. B |

Environmental Specification Notes:
Climatic Class: IEC 60068 55/155/56

Compliance Certifications (see [product page](#) for current document)

Plotted and Other Data

Notes:

4.3-10 Female Bulkhead Low PIM Connector Solder Attachment for TFT-5G-402



TC-402-4310F-BH-LP

4.3-10 Female Bulkhead Low PIM Connector Solder Attachment for TFT-5G-402 from Fairview Microwave is in-stock and available to ship same-day. All of our RF/microwave products are available off-the-shelf from our ISO 9001:2008 certified facilities in Lewisville, Texas. Fairview Microwave is RF on-demand.

For additional information on this product, please click the following link: [4.3-10 Female Bulkhead Low PIM Connector Solder Attachment for TFT-5G-402 TC-402-4310F-BH-LP](#)

URL: <https://www.fairviewmicrowave.com/4.3-10-female-tft-402-connector-tc-402-4310f-bh-lp-p.aspx>

The information contained within this document is accurate to the best of our knowledge and representative of the part described herein. It may be necessary to make modifications to the part and/or the documentation of the part in order to implement improvements. Fairview Microwave reserves the right to make such changes as required. Unless otherwise stated, all specifications are nominal. Fairview Microwave does not make any representation or warranty regarding the suitability of the part described herein for any particular purpose, and Fairview Microwave does not assume liability arising out of the use of any part or document.

TC-402-4310F-BH-LP CAD Drawing

4.3-10 Female Bulkhead Low PIM Connector Solder Attachment for TFT-5G-402

