

3 dBi WideBand Rubber Duck Antenna 860-960 MHz SMA Connector

The Fairview Microwave FM15RD1009 high performance 900 MHz omnidirectional “rubber-duck” antenna features a tilt-and-swivel SMA-Male connector, allowing them to be used vertically, at a right angle, or any angle in-between . It is a coaxial sleeve design with an omni-directional pattern. It is ideally suited for 900MHz ISM band applications as well as cellular applications.

The high performance rubber-duck FM51RD1009 from Fairview Microwave, measuring 8.62” long, is a flexible antenna providing broad coverage and 3 dBi gain. It is suitable as a replacement RF antenna for 900 MHz radios that are equipped with SMA-Male connectors such as wireless video transmitters and receivers, 900 MHz digital spread spectrum radios and more.

This rubber duck antenna, as well as our wide selection of superior quality RF devices, ship same day. Contact our knowledgeable and friendly technical support and sales staff for your answers on antennas or other Fairview Microwave products.

Configuration

Gain	3 to 3 dBi
Polarization	Vertical
Cable Type	Coax Cable
Connector Type	SMA Male
Number of Ports	1
Lightning Protection	DC Ground

Electrical Specifications

Description	Min	Typ	Max	Units
Frequency Range	860		960	MHz
Input VSWR			2:1	
Impedance		50		Ohms
Gain		3		dBi
Horizontal (Azimuth) Beam Width		360		Degrees
Vertical (Elevation) Beam Width		62		Degrees
Input Power			50	Watts

Specifications by Frequency

Description	Band 1	Band 2	Band 3	Band 4	Band 5	Units
Range	0.86-0.96					GHz
Gain	3					dBi
Horiz. Beam Width	360					Degrees
Vert. Beam Width	62					Degrees
Max Input Power	50					Watts

Mechanical Specifications

Size	
Length	8.62 in [218.95 mm]
Width	0.66 in [16.76 mm]
Height	0.66 in [16.76 mm]



Features:

- 900 MHz Omnidirectional
- Flexible Rubber Duck Antenna
- SMA Male Connector
- Tilt and Swivel Design

Applications:

- 900 MHz Digital Spread Spectrum Radios
- 900 MHz ISM Band
- 900 MHz Telemetry Products
- LoRA, IoT, M2M Applications
- Cellular Band Applications

Fairview Microwave
 301 Leora Ln., Suite 100
 Lewisville, TX 75056
 Tel: 1-800-715-4396 / (972) 649-6678
 Fax: (972) 649-6689
www.fairviewmicrowave.com
sales@fairviewmicrowave.com

Weight 0.049 lbs [22.23 g]

Environmental Specifications

Temperature

Operating Range -40 to +60 deg C

Environment UL 94HB

Compliance Certifications (see [product page](#) for current document)

Plotted and Other Data

Notes:

3 dBi WideBand Rubber Duck Antenna 860-960 MHz SMA Connector from Fairview Microwave is in-stock and available to ship same-day. All of our RF/microwave products are available off-the-shelf from our ISO 9001:2008 certified facilities in Lewisville, Texas. Fairview Microwave is RF on-demand.

For additional information on this product, please click the following link: [3 dBi WideBand Rubber Duck Antenna 860-960 MHz SMA Connector FM51RD1009](#)

URL: <https://www.fairviewmicrowave.com/wide-antenna-860-960-mhz-3-dbi-gain-sma-fm51rd1009-p.aspx>

The information contained in this document is accurate to the best of our knowledge and representative of the part described herein. It may be necessary to make modifications to the part and/or the documentation of the part, in order to implement improvements. Fairview Microwave reserves the right to make such changes as required. Unless otherwise stated, all specifications are nominal. Fairview Microwave does not make any representation or warranty regarding the suitability of the part described herein for any particular purpose, and Fairview Microwave does not assume any liability arising out of the use of any part or documentation.

