



Slide-On BMA Jack Bulkhead to Slide-On BMA Jack Bulkhead Cable RG405 Type .086 Coax

The BMA jack slide-on bulkhead to BMA jack slide-on bulkhead cable using RG405 type .086 coax, part number FMCA1587, from Fairview Microwave is in-stock and ships same day. This Fairview BMA to BMA cable assembly has a jack to jack gender configuration with 50 ohm semi-rigid FM-SR086CU coax. Fairview Microwave's semi-rigid RF cable assemblies are ideal for high performance applications and can be formed, using proper tooling, to the routing pattern required. The FMCA1587 BMA jack to BMA jack cable assembly operates to 18 GHz. Our RF cable assembly with BMA bulkhead interface allows designers to create external connections on their product enclosures, and can be used in a variety of other rack mount and panel mount applications.

Custom versions of most RF cable assemblies can be built and shipped same day. Custom cable assembly lengths can be obtained by specifying the desired length on the web site at time of order or by contacting a sales representative. Other RF cable assembly value added services including connector orientation or clocking, heat shrink booting and labeling are also available. RF testing can also be performed to document the electrical performance of your cable assembly.

Electrical Specifications

Description	Min	Т	ур	Max	Units
Frequency Range	DC			18	GHz
VSWR				1.5:1	
Return Loss				15.56	dB
Dielectric Withstanding \	Voltage (AC)			1,000	Vrms

Performance by Frequency

Description	F1	F2	F3	F4	F5	Units
Frequency	1	2	4.5	9	18	GHz
Insertion Loss (Typ.)	0.22	0.28	0.46	0.75	1.11	dB/ft
	0.72	0.92	1.51	2.46	3.64	dB/m

Electrical Specification Notes:

Insertion Loss does not include the loss of the connectors. Insertion Loss is estimated as 0.1 dB per connector.

Mechanical Specifications

Cable Assembly

Diameter 0.37 in [9.4 mm]

Cable

Cable Type
Impedance
Inner Conductor Type
Inner Conductor Material and Plating
Dielectric Type
Number of Shields
Outer Conductor Material and Plating

FM-SR086CU 50 Ohms Solid Copper Clad Steel, Silver PTFE 1 Copper



Configuration:

- Slide-On BMA Jack Bulkhead
- Slide-On BMA Jack Bulkhead
- FM-SR086CU

Features:

Max Frequency 18 GHz

Applications:

- General Purpose
- Laboratory Use
- Rack and Panel
- BMA Cable RF Backplanes
- Phased Array Interconnects
- High Speed Switching Networks
- Blind Mate BMA Test

Fairview Microwave 301 Leora Ln., Suite 100 Lewisville, TX 75056

Tel: 1-800-715-4396 / (972) 649-6678

Fax: (972) 649-6689 www.fairviewmicrowave.com sales@fairviewmicrowave.com





Repeated Minimum Bend Radius 0.05 in [1.27 mm]

Connectors

Connector 1	Connector 2
BMA Jack	BMA Jack
Bulkhead	Bulkhead
50 Ohms	50 Ohms
Connection Method Slide-On	
t Material & Plating Beryllium Copper, Gold	
ng Beryllium Copper, G	old Beryllium Copper, Gold
Brass, Tri-Metal	Brass, Tri-Metal
	BMA Jack Bulkhead 50 Ohms Slide-On Beryllium Copper, G ng Beryllium Copper, G

Mechanical Specification Notes:

Environmental Specifications

Temperature

Operating Range

-55 to +105 deg C

Compliance Certifications (see product page for current document)

Plotted and Other Data


Notes:

^{*}All cable assemblies have a length tolerance of 1.5% or \pm 3/8", whichever is greater.





Typical Performance Data



How to Order

Example: FMCA1587-12 = 12 inches long cable

FMCA1587-100cm = 100 cm long cable






Slide-On BMA Jack Bulkhead to Slide-On BMA Jack Bulkhead Cable RG405 Type .086 Coax from Fairview Microwave has same day shipment for domestic and International orders. Our RF, microwave and fiber optic products maintain a 99% availability and are part of the broadest selection in the industry.


Click the following link to obtain additional part information: Slide-On BMA Jack Bulkhead to Slide-On BMA Jack Bulkhead Cable RG405 Type .086 Coax FMCA1587

URL: https://www.fairviewmicrowave.com/bma-jack-bma-jack-cable-rg405-type-.086-coax-fmca1587-p.aspx









STANDARD TOLERANCES
,X ±0.2
,XX ±0.01
,XXX ±0.005

*STANDARD TOLERANCES APPLY ONLY TO DIMENSIONS IN INCHES

FAIRVIEW MICROWAVE INC. ALLEN, TX 75013 WWW.FAIRVIEWMICROWAVE.COM	NOTES: 1. UNLESS OTHERWISE SPECIFIED ALL DIMENSIONS ARE NOMINAL, 2. ALL SPECIFICATIONS ARE SUBJECT TO CHANGE WITHOUT NOTICE AT ANY TIME, 3. DIMENSIONS ARE IN INCHES [mm].					
Slide-On BMA Jack Bulkhead to Slide-On BMA Jack Bulkhead Cable RG405 Type .086 Coax	DWG NO FMCA1587			CAGE CODE 3FKR5		
	CAD FILE 12/18/17	SHEET	SCAL	LE N/A SIZE A	CN2245	