

# 2.92mm Male to 2.4mm Male Cable Using FM-103FLEX Coax

The 2.92mm male to 2.4mm male cable using FM-103FLEX coax, part number FMCA1977, from Fairview Microwave is in-stock and ships same day. This Fairview 2.92mm to 2.4mm cable assembly has a male to male gender configuration with 50 ohm flexible FM-103FLEX coax. Fairview Microwave's flexible RF cable assemblies are ideal for applications where tight bends and continual flexure are required. The FMCA1977 2.92mm male to 2.4mm male cable assembly operates to 45 GHz. The triple shielding of this Fairview cable assembly provides excellent shielding effectiveness of better than 90 dB.

Custom versions of most RF cable assemblies can be built and shipped same day. Custom cable assembly lengths can be obtained by specifying the desired length on the web site at time of order or by contacting a sales representative. Other RF cable assembly value added services including connector orientation or clocking, heat shrink booting and labeling are also available. RF testing can also be performed to document the electrical performance of your cable assembly.

### **Electrical Specifications**

Description	Min	Тур	Мах	Units
Frequency Range	DC		45	GHz
VSWR			1.4:1	
Velocity of Propagation		76		%
RF Shielding	90			dB
Capacitance		26 [ <mark>85.3]</mark>		pF/ft [pF/m]
Inductance		65 [2 <mark>13.25</mark> ]		uH/ft [uH/m]
Input Power (Peak)			550	Watts

#### Performance by Frequency

		-				
Description	F1	F2	F3	F4	F5	Units
Frequency	2.5	5	10	20	45	GHz
Insertion Loss (Max.)	0.64	0.84	1.12	1.55	2.34	dB/ft
	2.1	2.76	3.67	5.09	7.68	dB/m
Insertion Loss (Typ.)	0.6	0.78	1.04	1.43	2.14	dB/ft
	1.97	2.56	3.41	4.69	7.02	dB/m

### **Mechanical Specifications**

Cable Assembly Diameter

#### Cable

Cable Type Impedance Inner Conductor Type Inner Conductor Material and Plating Dielectric Type Number of Shields 0.38 in [9.65 mm]

FM-103FLEX 50 Ohms Stranded Copper, Silver PTFE 3



**FMCA1977** 

**DATA SHEET** 

# **Configuration:**

- 2.92mm Male
- 2.4mm Male
- FM-103FLEX

## **Features:**

- Max Frequency 45 GHz
- Shielding Effectivity > 90 dB
- 76% Phase Velocity
- Triple Shielded
- ETFE Jacket

# **Applications:**

- General Purpose
- Laboratory Use

Fairview Microwave 301 Leora Ln., Suite 100 Lewisville, TX 75056 Tel: 1-800-715-4396 / (972) 649-6678 Fax: (972) 649-6689 www.fairviewmicrowave.com sales@fairviewmicrowave.com Fairview Microwave

# an INFINIT<sup>C</sup> brand

FMCA1977 DATA SHEET

Shield Layer 1 Shield Layer 2 Shield Layer 3 Jacket Material Jacket Diameter Silver Plated Copper Conductive Tape Silver Plated Copper ETFE, Gray 0.103 in [2.62 mm]

One Time Minimum Bend Radius Repeated Minimum Bend Radius Typical Flex Cycles 0.32 in [8.13 mm] 0.96 in [24.38 mm] 500,000

### Connectors

Description	Connector 1	Connector 2
Туре	2.92mm Male	2.4mm Male
Impedance	50 Ohms	50 Ohms
Contact Material & Plating	Beryllium Copper, (	Gold Beryllium Copper, Gold
Contact Plating Spec.	ASTM-B488 50µ In	. <mark>Min ASTM-B488 50µ In. Mini</mark> mu
Dielectric Type	PPO	PPO
Body Material & Plating	Passivated Stainless	Steel Passivated Stainless Steel
Body Plating Spec.	SAE-AMS-2700	SAE-AMS-2700
Coupling Nut Material & Pla	ating Passivated Stainless	Steel Passivated Stainless Steel
Coupling Nut Plating Spec.	SAE-AMS-2700	SAE-AMS-2700
Hex Size	5/16 Inch	5/16 Inch
Torque	8 in-lbs 0.9 Nn	n 8 in-lbs 0.9 Nm

Mechanical Specification Notes:

\*All cable assemblies have a length tolerance of 1.5% or  $\pm$  3/8", whichever is greater.

## **Environmental Specifications**

Temperature	
<b>Operating Range</b>	ļ

-45 to +125 deg C

**Compliance Certifications** (see product page for current document)

### Plotted and Other Data


Notes:

• Values at 25°C, sea level.

### **How to Order**

Part Number Configuration:

FMCA1977 - xx uu



Example: FMCA1977-12 = 12 inches long cable FMCA1977-100cm = 100 cm long cable

301 Leora Ln., Suite 100, Lewisville, TX 75056 | Tel: 1-800-715-4396 / (972) 649-6678 / Fax: (972) 649-6689






2.92mm Male to 2.4mm Male Cable Using FM-103FLEX Coax from Fairview Microwave has same day shipment for domestic and International orders. Our RF, microwave and fiber optic products maintain a 99% availability and are part of the broadest selection in the industry.

Click the following link to obtain additional part information: 2.92mm Male to 2.4mm Male Cable Using FM-103FLEX Coax FMCA1977


URL: https://www.fairviewmicrowave.com/2.92mm-male-2.4mm-male-FM-103FLEX-cable-assembly-FMCA1977-p.aspx



301 Leora Ln., Suite 100, Lewisville, TX 75056 | Tel: 1-800-715-4396 / (972) 649-6678 / Fax: (972) 649-6689







301 Leora Ln., Suite 100, Lewisville, TX 75056 | Tel: 1-800-715-4396 / (972) 649-6678 / Fax: (972) 649-6689