Fairview Microwave

an INFINIT[®] brand

2.92mm Female Connector Field Replaceable Attachment 2 Hole Flange , .481 inch Hole Spacing 0.02 inch Pin with Metal Contact Ring

2.92mm female 2 hole flange mount field replaceable connector with EMI gasket (.481 inch hole spacing), part number FMCN1651, from Fairview Microwave is in-stock and ships same day. This 2.92mm female connector operates up to a maximum frequency of 40 GHz and offers excellent VSWR of 1.2:1. Fairview's FMCN1651 2 hole flange 2.92mm connector enables designers to make external connections on product enclosures, and can be used in a variety of other rack mount and panel mount applications. Fairview's field replaceable connector is easy to install or replace in the field.

Fairview's 2.92mm female 2 hole flange connector FMCN1651 datasheet specifications and outline drawing are shown in this PDF below. Our extensive offering of RF, microwave and millimeter wave connectors allows designers to configure and customize their signal connections however they like. From providing an I/O for a board design to creating a custom cable assembly configuration, Fairview Microwave has a connector solution to meet your needs. Fairview Microwave also has the expertise to build your custom cable assemblies for you and ship them same-day.

Electrical Specifications

Description	Min	Тур	Max	Units
Frequency Range	DC		40	GHz
VSWR			1.2:1	

Mechanical Specifications

Size	
Length	0.372 in [9.45 mm]
Width/Dia.	0.25 in [6.35 mm]
Height	0.625 in [15.88 mm]
Weight	0.00725 lbs [3.29 g]
Mating Cycles	500 Cycles

Material Specifications

Material	Plating	
Beryllium Copper	Gold	
PEI		
Passivated Stainless Steel		
Passivated Stainless Steel		
	Beryllium Copper PEI Passivated Stainless Steel	

Environmental Specifications

Temperature Operating Range

-40 to +165 deg C

Compliance Certifications (see product page for current document)

Plotted and Other Data

Notes:





Configuration:

- 2.92mm Female Connector
- Straight Body Geometry
- 0.02 inch Pin Interface Type
- Field Replaceable Attachment
- 2 Hole Flange

Features:

- Operating Frequency of 40 GHz Max.
- Excellent VSWR of 1.2:1
- Gold Plated Beryllium Copper Contact
- Metal Contact Ring

Applications:

- General Purpose Test
- Rack and Panel Mount Applications
- Used in Product Requiring
 Hermetic Seals
- Allows for Replacement of Damaged Connectors


Fairview Microwave 301 Leora Ln., Suite 100 Lewisville, TX 75056 Tel: 1-800-715-4396 / (972) 649-6678 Fax: (972) 649-6689 www.fairviewmicrowave.com sales@fairviewmicrowave.com an INFINIT[®] brand



2.92mm Female Connector Field Replaceable Attachment 2 Hole Flange , .481 inch Hole Spacing 0.02 inch Pin with Metal Contact Ring from Fairview Microwave is in-stock and available to ship same-day. All of our RF/microwave products are available off-the-shelf from our ISO 9001:2008 certified facilities in Lewisville, Texas. Fairview Microwave is RF on-demand.

For additional information on this product, please click the following link: 2.92mm Female Connector Field Replaceable Attachment 2 Hole Flange , .481 inch Hole Spacing 0.02 inch Pin with Metal Contact Ring FMCN1651

URL: https://www.fairviewmicrowave.com/2.92mm-female-0.02-pin-connector-fmcn1651-p.aspx




301 Leora Ln., Suite 100, Lewisville, TX 75056 | Tel: 1-800-715-4396 / (972) 649-6678 / Fax: (972) 649-6689

Fairview Microwave

FMCN1651 DATA SHEET

an INFINIT[®] brand



301 Leora Ln., Suite 100, Lewisville, TX 75056 | Tel: 1-800-715-4396 / (972) 649-6678 / Fax: (972) 649-6689