Fairview Microwave

## an INFINIT<sup>©</sup> brand

# 2.4mm Female Connector Field Replaceable Attachment 2 Hole Flange 0.015 inch Pin, .355 inch Hole Spacing with Metal Contact Ring

2.4mm female 2 hole flange mount field replaceable connector with EMI gasket, part number FMCN1674, from Fairview Microwave is in-stock and ships same day. This 2.4mm female connector operates up to a maximum frequency of 50 GHz and offers excellent VSWR of 1.2:1. Fairview's FMCN1674 2 hole flange 2.4mm connector enables designers to make external connections on product enclosures, and can be used in a variety of other rack mount and panel mount applications. Fairview's field replaceable connector is easy to install or replace in the field.

Fairview's 2.4mm female 2 hole flange connector FMCN1674 datasheet specifications and outline drawing are shown in this PDF below. Our extensive offering of RF, microwave and millimeter wave connectors allows designers to configure and customize their signal connections however they like. From providing an I/O for a board design to creating a custom cable assembly configuration, Fairview Microwave has a connector solution to meet your needs. Fairview Microwave also has the expertise to build your custom cable assemblies for you and ship them same-day.

#### **Electrical Specifications**

Description	Min	Тур	Мах	Units
Frequency Range	DC		50	GHz
VSWR			1.2:1	

### **Mechanical Specifications**

<b>Size</b> Length	0.427 in [10.85 mm]
Width/Dia. Height	0.275 in [6.99 mm] 0.5 in [12.7 mm]
Weight	0.7 lbs [317.51 g]
Mating Cycles	500 Cycles

#### **Material Specifications**

Material	Plating	
Beryllium Copper	Gold	
PEI		
Passivated Stainless Steel		
Passivated Stainless Steel		
	Beryllium Copper PEI Passivated Stainless Steel	

#### **Environmental Specifications**

**Temperature** Operating Range

-40 to +165 deg C

Compliance Certifications (see product page for current document)

### **Plotted and Other Data**

Notes:





# **Configuration:**

- 2.4mm Female Connector
- Straight Body Geometry
- 0.015 inch Pin Interface Type
- Field Replaceable Attachment
- 2 Hole Flange

# Features:

- Operating Frequency of 50 GHz Max.
- Excellent VSWR of 1.2:1
- Gold Plated Beryllium Copper Contact
- Metal Contact Ring

## **Applications:**

- General Purpose Test
- Rack and Panel Mount Applications
- Used in Product Requiring
  Hermetic Seals
- Allows for Replacement of Damaged Connectors


Fairview Microwave 301 Leora Ln., Suite 100 Lewisville, TX 75056 Tel: 1-800-715-4396 / (972) 649-6678 Fax: (972) 649-6689 www.fairviewmicrowave.com sales@fairviewmicrowave.com an INFINIT® brand



2.4mm Female Connector Field Replaceable Attachment 2 Hole Flange 0.015 inch Pin, .355 inch Hole Spacing with Metal Contact Ring from Fairview Microwave is in-stock and available to ship same-day. All of our RF/microwave products are available off-the-shelf from our ISO 9001:2008 certified facilities in Lewisville, Texas. Fairview Microwave is RF on-demand.

For additional information on this product, please click the following link: 2.4mm Female Connector Field Replaceable Attachment 2 Hole Flange 0.015 inch Pin, .355 inch Hole Spacing with Metal Contact Ring FMCN1674


URL: https://www.fairviewmicrowave.com/2.4mm-female-0.015-pin-connector-fmcn1674-p.aspx



301 Leora Ln., Suite 100, Lewisville, TX 75056 | Tel: 1-800-715-4396 / (972) 649-6678 / Fax: (972) 649-6689

an INFINIT© brand





301 Leora Ln., Suite 100, Lewisville, TX 75056 | Tel: 1-800-715-4396 / (972) 649-6678 / Fax: (972) 649-6689