


SPECIFICATIONS

ELECTRICAL:

FREQUENCY: 0-3 GHZ
 VSWR 1.15 MAX
 POWER (AVG) 2 WATTS
 POWER (PEAK) 250 WATTS
 IMPEDANCE: 50 OHMS
 ATTENUATION ACCURACY:
 GREATER OF +/- .3 DB OR 3%



MECHANICAL:

MATERIAL BODY: BRASS
 PLATING: TRI-METAL (TIN-ZINC-COPPER)
 MATERIAL RING & CONTACTS: BeCu
 CENTER CONTACT: GOLD PLATED PER MIL-G-45204
 RESISTIVE ELEMENT: AINi SUBSTRATE Ta Ni RESISTOR

ENVIRONMENTAL:

TEMP: -55 C TO +125 C

				FAIRVIEW MICROWAVE INC.	
				ALLEN, TX 75013 WWW.FAIRVIEWMICROWAVE.COM	
				TITLE	
				ATTENUATORS SMA M/F 3GHZ	
SIZE	CAGE CODE	DWG NO			REV
A	3FKR5	SA03-XX			A
SCALE			SHEET		