

SA3S5W-30 DATA SHEET

30 dB Fixed Attenuator SMA Male To SMA Female Up To 3 GHz Rated To 5 Watts With Aluminum Body

Fairview Microwave carries a broad selection of fixed attenuators with a wide range of attenuation levels, frequency ranges, and power dissipation ranges. Also known as RF pads, RF microwave attenuators lower the amplitude of a signal (or attenuate) a known amount. These attenuator pads can be used in a wide variety of applications including reducing a signal level to protect measurement equipment or other circuitry, extending the range of power meters and amplifiers, and impedance matching circuits by reducing the VSWR seen by adjacent components. RF attenuators can prevent signal overload in amplifiers, receivers and detectors, adjusting the signal level to a range that is optimal.

Few RF components are as commonly used as fixed coaxial attenuators, and Fairview Microwave carries one of the largest in-stock selections and ships them same day. The SA3S5W-30 is a 30 dB Fixed Attenuator that operates from DC to 3 GHz and is rated to 5 Watts. The versatile coaxial package uses SMA male to SMA female connectors and is also REACH and RoHS compliant.

Electrical Specifications

•				
Description	Min	Тур	Max	Units
Frequency Range	DC		3	GHz
Impedance		50		Ohms
Nominal Attenuation		30		dB
Attenuation Accuracy			±0.7	dB
VSWR			1.25:1	
Input Power, CW derated linearly to .5V	√ @125°C		5	Watts
Input Power, Peak			500	Watts

Mechanical Specifications

SizeLength2.76 in [70.1 mm]Width/Diameter0.71 in [18.03 mm]Weight0.11 lbs [49.9 g]Body Material and PlatingAluminum

Configuration

Design Fixed, Bidirectional Package Style Connectorized

Connectors

Description	Connector 1	Connector 2		
Туре	SMA Male	SMA Female		
Contact Material & Plating	Brass, Gold	Beryllium Copper, Gold		
Outer Conductor Material & Plating	Brass, Nickel	Brass, Nickel		
Coupling Nut Material & Plating	Brass, Nickel			
Hex Size	5/16 inch			



Features:

- Bidirectional
- DC to 3 GHz Frequency Range
- Attenuation 6±0.4 dB
- Max Power 5 Watts (CW)
- VSWR < 1.25:1

Applications:

- Instrumentation
- Precision Measurements
- Prototyping and Characterization
- · Production Systems

Fairview Microwave 1130 Junction Dr. #100 Allen, TX 75013

Tel: 1-800-715-4396 / (972) 649-6678

Fax: (972) 649-6689 www.fairviewmicrowave.com sales@fairviewmicrowave.com





Torque 5 in-lbs [0.57 Nm]

Body Material & Plating Brass, Nickel Brass, Nickel

Environmental Specifications

Temperature


Operating Range -55 to +125 deg C

Compliance Certifications (visit www.FairviewMicrowave.com for current document)

RoHS Compliant Yes

REACH Compliant 12/17/2014

Plotted and Other Data Notes: Typical Performance Data



30 dB Fixed Attenuator SMA Male To SMA Female Up To 3 GHz Rated To 5 Watts With Aluminum Body from Fairview Microwave is in-stock and available to ship same-day. All of our RF/microwave products are available off-the-shelf from our ISO 9001:2008 certified facilities in Allen, Texas. Fairview Microwave is RF on-demand.

For additional information on this product, please click the following link: 30 dB Fixed Attenuator SMA Male To SMA Female Up To 3 GHz Rated To 5 Watts With Aluminum Body SA3S5W-30

URL: http://www.fairviewmicrowave.com/30db-fixed-attenuator-sma-male-sma-female-5-watts-sa3s5w-30-p.aspx

The information contained in this document is accurate to the best of our knowledge and representative of the part described herein. It may be necessary to make modifications to the part and/or the documentation of the part, in order to implement improvements. Fairview Microwave reserves the right to make such changes as required. Unless otherwise stated, all specifications are nominal. Fairview Microwave does not make any representation or warranty regarding the suitability of the part described herein for any particular purpose, and Fairview Microwave does not assume any liability arising out of the use of any part or documentation.


1130 Junction Dr. #100 Allen, TX 75013 | Tel: 1-800-715-4396 / (972) 649-6678 / Fax: (972) 649-6689

Copyright © 2016 REV 1.1 Page 2 of 3





P/N	Atten.		
SA3S5W-03	3 dB		
SA3S5W-10	10 dB		
SA3S5W-20	20 dB		
SA3S5W-30	30 dB		



FAIRVIEW MICROWAVE INC. ALLEN, TX 75013 WWW.FAIRVIEWMICROWAVE.COM	NOTES: 1. UNLESS OTHERWISE SPECIFIED ALL DIMENSIONS ARE NOMINAL. 2. ALL SPECIFICATIONS ARE SUBJECT TO CHANGE WITHOUT NOTICE AT ANY TIME. 3. DIMENSIONS ARE IN INCHES [mm].				
30 dB Fixed Attenuator SMA Male To SMA Female Up To 3 GHz Rated To 5 Watts With Aluminum Body	DWG NO SA3S5W		C	CAGE CODE 3FKR5	
	CAD FILE 102115	SHEET	SCALE	N/A	SIZE A