

TRS Jack RFI Cap with 3" Stainless Steel Lanyard and .439-.443" D-Ring

Mechanical Specifications

Configuration

Connector
Chain Option 3 in Chain
Mating Cycles 500 Cycles

Description	Material	Plating
Body	Brass	Nickel
Coupling Nut	Brass	Nickel
Gasket	Silicone	
Chain	Stainless Steel	Nylon Jacket
Rivet	Brass	Nickel

Size

Length 4.4 in [111.76 mm]
Width 0.46 in [11.68 mm]
Height 0.46 in [11.68 mm]
Weight 0.01 lbs [4.54 g]

Environmental Specifications

Temperature

Operating Range -65 to +165 deg C

Compliance Certifications (see [product page](#) for current document)

Plotted and Other Data

Notes:

TRS Jack RFI Cap with 3" Stainless Steel Lanyard and .439-.443" D-Ring from Fairview Microwave is in-stock and available to ship same-day. All of our RF/microwave products are available off-the-shelf from our ISO 9001:2008 certified facilities in Lewisville, Texas. Fairview Microwave is RF on-demand.


For additional information on this product, please click the following link: [TRS Jack RFI Cap with 3" Stainless Steel Lanyard and .439-.443" D-Ring SC10-06305](#)

URL: <https://www.fairviewmicrowave.com/dust-cap-3-inch-chain-sc10-06305-p.aspx>

The information contained in this document is accurate to the best of our knowledge and representative of the part described herein. It may be necessary to make modifications to the part and/or the documentation of the part, in order to implement improvements. Fairview Microwave reserves the right to make such changes as required. Unless otherwise stated, all specifications are nominal. Fairview Microwave does not make any representation or warranty regarding the suitability of the part described herein for any particular purpose, and Fairview Microwave does not assume any liability arising out of the use of any part or documentation.



Fairview Microwave
301 Leora Ln., Suite 100
Lewisville, TX 75056
Tel: 1-800-715-4396 / (972) 649-6678
Fax: (972) 649-6689
www.fairviewmicrowave.com
sales@fairviewmicrowave.com



TRS Jack RFI Cap with 3" Stainless Steel Lanyard and .439-.443" D-Ring

THE INFORMATION CONTAINED IN THIS DRAWING IS THE SOLE PROPERTY OF INFINITE ELECTRONICS, INC. ANY REPRODUCTION IN WHOLE OR IN PART WITHOUT THE WRITTEN AUTHORIZATION OF INFINITE ELECTRONICS, INC. IS PROHIBITED. THESE COMMODITIES, TECHNOLOGY OR SOFTWARE WERE EXPORTED FROM THE UNITED STATES IN ACCORDANCE WITH THE EXPORT ADMINISTRATION REGULATIONS. DIVERSION CONTRARY TO U.S. LAW PROHIBITED.

Fairview Microwave[®] an INFINIT [®] brand Website: www.FairviewMicrowave.com Phone: 1.800.715.4396 1.972.649.6678		INTERPRET ALL DIMENSIONS AND TOLERANCES PER ASME Y14.5 SCALE: NONE SHEET: 1 OF 1
DESCRIPTION TRS JACK RFI CAP W/3 INCH SST LANYARD AND .439 D-RING		
UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE IN INCHES. DIMENSIONS IN [] ARE IN MILLIMETERS.	TOLERANCES: .X = ±.2 [5] .XX = ±.02 [.5] .XXX = ±.005 [.13]	FRACTIONS ± 1/32 ANGLES ± 1°
CABLE LENGTH TOLERANCES: ≤ 12 [305] = ± 1/25 / -0 > 12 [305] ≤ 60 [1524] = +2 [51] / -0 > 60 [1524] ≤ 120 [3048] = +4 [102] / -0 > 120 [3048] ≤ 300 [7620] = +6 [152] / -0 > 300 [7620] = +5% / -0		
ALL DIMENSIONS ARE FOR REFERENCE ONLY AND SUBJECT TO CHANGE WITHOUT NOTICE.		
SIZE A CAGE CODE 3FKR5	DRAWN BY DFRISIELLO	ITEM NO. SC10-06305 REV A