

SMA/MRA-SMA/MRA FLEXIBLE CABLES 1GHZ RG58CU

SCB15185-XX


SPECIFICATIONS

CABLE ASSEMBLY:
VSWR:1.2:1 @<1GHZ TYPICAL

RAW CABLE: RG58CU
TYPICAL LOSS (EXCLUDING CONNECTORS)
@1GHz: 0.15 DB/FT
@2GHz: 0.22 DB/FT

CONNECTORS:
SMA: BRASS torque 5-in-lbs
CONTACTS Au PLATING
INTERFACE: MIL-STD-348A

OP TEMP: -55-110°C
ROHS COMPLIANT



FAIRVIEW MICROWAVE INC.

ALLEN, TX 75013 WWW.FAIRVIEWMICROWAVE.COM

TITLE

SMA/MRA-SMA/MRA FLEXIBLE CABLES
1GHZ RG58CU

SIZE	CAGE CODE	DWG NO	REV
A	3FKR5	SCB15185-XX	--
SCALE		SHEET	

ALL DIMENSIONS IN inches(MM) Typical