

SMA/M/RA-SMA/M/RA FLEXIBLE CABLES RG174 3 GHZ

SCB15189-XX

SPECIFICATIONS


CABLE ASSEMBLY:
VSWR: 1.2:1 TYPICAL @ 3GHZ

RAW CABLE: RG174
LOSS (EXCLUDING CONNECTORS)
@ 1GHZ: 0.27 DB/FT
@ 2GHZ: 0.39 DB/FT
@ 3GHZ: 0.49 DB/FT


OD DIAMETER: .11"

CONNECTORS:
SMA: NICKEL PLATED BRASS
INTERFACE: MIL-STD-348A
CONTACTS: Au PLATTING

TORQUE 5 IN-IBS



MEASUREMENTS BELOW ARE TYPICAL



ALL DIMENSIONS IN inches(MM) Typical

FAIRVIEW MICROWAVE

FAIRVIEW, TX WWW.FAIRVIEWMICROWAVE.COM

TITLE

SMA/M/RA-SMA/M FLEXIBLE CABLES RG174 3GHZ

SIZE	CAGE CODE	DWG NO	REV
A	3FKR5	SCB15189-XX	A
SCALE	SHEET		