

SMA/M/RA-SMA/M/RA FLEXIBLE CABLES RG316DS 3GHZ

SCB15808-XX

SPECIFICATIONS


CABLE ASSEMBLY:
VSWR: <1.2 TYPICAL @ 3GHZ

RAW CABLE: RG316DS
LOSS (EXCLUDING CONNECTORS)
@ 1GHZ: 0.28 DB/FT
@ 2GHZ: 0.42 DB/FT
@ 3GHZ: 0.51 DB/FT


OVERALL DIAMETER: .163"

CONNECTORS:
SMA: NICKEL PLATED BRASS
INTERFACE: MIL-STD-348A
CONTACTS; BRASS Au PLATTING

TORQUE 5 IN-IBS



MEASUREMENTS BELOW ARE TYPICAL



ALL DIMENSIONS IN inches(MM) Typical

FAIRVIEW MICROWAVE

FAIRVIEW, TX WWW.FAIRVIEWMICROWAVE.COM

TITLE

SMA/M/RA-SMA/M/RA FLEXIBLE CABLES RG316DS 3GHZ

SIZE	CAGE CODE	DWG NO	REV
A	3FKR5	SCB15808-XX	A
SCALE	SHEET		