









## NOTES:

- FINISH (PLATING THICKNESS IN MICRO-INCHES)

   BERYLLIUM COPPER.
- GOLD PL. 4 MIN. OVER NICKEL-PHOSPHORUS ALLOY PL. 80 MIN. OVER COPPER PL. 20MIN.

THESE COMMODITIES, TECHNOLOGY OR SOFTWARE WERE EXPORTED FROM THE UNITED STATES IN ACCORDANCE WITH THE EXPORT ADMINISTRATION REGULATIONS. DIVERSION CONTRARY TO U.S. LAW PROHIBITED.



TIT IE

an INFINIT® brand

A |  $X = \pm .2$  [5.08]  $XX = \pm .02$  [.51]  $XXX = \pm .005$  [.13] UNLESS OTHERWISE SPECIFIED LEADING DIMENSIONS ARE INCHES DIMENSIONS IN [] ARE MILLIMETERS CAGE CODE 3FKR5 ALL DIMENSIONS SHOWN ARE FOR REFERENCE ONLY. TOLERANCES: FRACTIONS ± 1/32 ANGLES ± 1° DRAWN BY
K.DANG L ≤ 12 [305] = +1 [25] / -0
12 [305] < L ≤ 60 [1624] = +2 [51] / -0
60 [1524] < L ≤ 120 [3048] = +4 [102] / -0
120 [3048] < L ≤ 300 [7620] = +6 [182] / -0
300 [7620] < L = +5%L / -0 CABLE LENGTH (L) TOLERANCES: ITEM NO. FM1016-14 THE INFORMATION AND DESIGN IN THIS DOCUMENT IS THE PROPERTY OF FAIRVIEW MICKOWAVE CORPORATION.
ALL RIGHTS RESERVED. SHEET SCALE NGLE PROJECTION N/A REV