


	מ	
В	REV.	
PCR FM2CP1125-30	DESCRIPTION	REVISIONS
8/11/2021	DATE	
S.PONG	APPROVED	







LABEL

FAIRVIEW MICROWAVE FM2CP1125-30 D/C: YYWW

THESE COMMODITIES, TECHNOLOGY OR SOFTWARE WERE EXPORTED FROM THE UNITED STATES IN ACCORDANCE WITH THE EXPORT ADMINISTRATION REGULATIONS. DIVERSION CONTRARY TO U.S. LAW PROHIBITED.



an INFINIT® brand

TITLE

⊳	SIZE		X = ±.2 [5.08] FRACTIONS XX = ±.02 [.51] ±.132 XXX = ±.005[.13] ANGLES ± 1°						UNI
<u>ع</u>	CAGE CODE	ALL DIM					TOLERANCES	SSCIHER	SS OTHER
3FKR5		ENSIONS SHO	FRACTIONS ± 1/32 ANGLES ± 1°			0.00	NCES:	DIMENSIONS	WISE SPECIF
K.DANG	DRAWN BY	ALL DIMENSIONS SHOWN ARE FOR REFERENCE ONLY.			02000	CABLELENGTH	DIMENSIONS IN [] ARE MILLIMETERS	UNLESS OTHERWISE SPECIFIED LEADING DIMENSIONS ARE INCHES	
FM2CP1125-30	ITEM NO.	NCE ONLY.	12 [305] < L5 (12 [305] = 14 [25]) / Ju 12 [305] < L5 (01 [524] = 12 [51] / Ju 60 [1524] < L5 (120 [3048] = 14 [102]) / Ju 120 [3048] < L5 (300 [7620] = 16 [152]) / Ju 300 [7620] < L5 (152) / Ju 300 [7620] < L5			CABLE LENGTH (L) TOLERANCES:		ONS ARE INCHES	
1125-30		SCALE N	SHEET 1	FAIRVIEW MICROWAVE CORPORATION ALL RIGHTS RESERVED.	DESIGN IN THIS DOCUMENT	THE INFORMATION AND	-(	₽	THIRD-ANGLE PROJECTION
Φ	REV	N/A	¥ 1	CORPORATION. SERVED.	DOCUMENT RTY OF	ION AND	_	-	OJECTION