

Fairview Microwave THESE COMMODITIES, TECHNOLOGY OR SOFTWARE WERE EXPORTED FROM THE UNITED STATES IN ACCORDANCE WITH THE EXPORT ADMINISTRATION REGULATIONS. DIVERSION CONTRARY TO U.S. LAW PROHIBITED.

UNLESS OTHERWISE SPECIFIED LEADING DIMENSIONS ARE INCHES DIMENSIONS IN [] ARE MILLIMETERS.  $X = \pm .2$  [5.08] FRACTIONS  $XX = \pm .02$  [.51]  $\pm .1/32$   $XXX = \pm .005$  [.13] ANGLES  $\pm .1^{\circ}$ ALL DIMENSIONS SHOWN ARE FOR REFERENCE ONLY. L ≤ 12 [305] = +1 [25] / -0
12 [305] < L ≤ 60 [1624] = +2 [51] / -0
60 [1524] < L ≤ 120 [3048] = +4 [102] / -0
120 [3048] < L ≤ 300 [7620] = +6 [182] / -0
300 [7620] < L = +5%L / -0 CABLE LENGTH (L) TOLERANCES:

A CAGE CODE 3FKR5

DRAWN BY ITEM NO. MVEERAPPAN

FMAD1215

N/A

REV

THE INFORMATION AND DESIGN IN THIS DOCUMENT IS THE PROPERTY OF FAIRVIEW MICKOWAVE CORPORATION.
ALL RIGHTS RESERVED.

TITLE

an INFINIT® brand