

REV. ≻ INITIAL RELEASE DESCRIPTION REVISIONS 03/31/2022 DATE A.GANWANI APPROVED



Ø.571 [14.50] MAX -STRAIGHT KNURL 1.10 [27.9] 250 HEX

BNC MALE

SSMA MALE

Fairview Microwave THESE COMMODITIES, TECHNOLOGY OR SOFTWARE WERE EXPORTED FROM THE UNITED STATES IN ACCORDANCE WITH THE EXPORT ADMINISTRATION REGULATIONS, DIVERSION CONTRARY TO US. LAW PROHIBITED.

' Microwave

UNLESS OTHERWISE SPECIFIED LEADING DIMENSIONS ARE INCHES DIMENSIONS IN [] ARE MILLIMETERS.

TOLERANCES:

CABLE LENGTH (L) TOLERANCES:

NGLE PROJECTION

an INFINIT® brand

X = ±.2 [5.08] FRACTIONS XX = ±.02 [.51] ± 1/32 XXX = ±.005[.13] ANGLES ± 1° ⊳ CAGE CODE 3FKR5 ALL DIMENSIONS SHOWN ARE FOR REFERENCE ONLY. K.GLEBOVA L ≤ 12 [305] = +1 [25] / 0
12 [305] < L ≤ 60 [1624] = +2 [51] / 0
60 [1524] < L ≤ 120 [3048] = +4 [102] / 0
120 [3048] < L ≤ 300 [7620] = +6 [182] / 0
300 [7620] < L = +5%L / 0 ITEM NO. FMAD1289 THE INFORMATION AND DESIGN IN THIS DOCUMENT IS THE PROPERTY OF FAIRVIEW MICKOWAVE CORPORATION.
ALL RIGHTS RESERVED. SCALE

N/A

REV