
| Þ | REV. | |
|-----------------|-------------|-----------|
| INITIAL RELEASE | DESCRIPTION | REVISIONS |
| 03/31/2022 | DATE | |
| AGANWANI | APPROVED | |
| | | |



MALE

1.85mm FEMALE

THESE COMMODITIES, TECHNOLOGY OR SOFTWARE WERE EXPORTED FROM THE UNITED STATES IN ACCORDANCE WITH THE EXPORT ADMINISTRATION REGULATIONS. DIVERSION CONTRARY TO U.S. LAW PROHIBITED.

** Microwave

**Unless otherwise specified leading dimensions are inches dimensions in [] are millimeters.



TITLE

| A | 01330 | FMAD1330 | K.GLEBOVA | 3FKK5 | 4 |
|---|--|--|--|------------------------------------|------------------------------|
| REV | | ITEM NO. | DRAWN BY |) 1 | CAGE CODE |
| A A | SCALE N/A | NCE ONLY. | ALL DIMENSIONS SHOWN ARE FOR REFERENCE ONLY. | ENSIONS SHOV | ALL DIV |
| <u> </u> | SHEET 1 OF | L \(\frac{300}{7620} \] \(\text{L} \) \(\frac{152}{7} \) \(\text{-0} \) \(\frac{152}{7} \) \(1 | 120 [3048] < L ≤ 300 [7620] = +6 [152] / -0 300 [7620] < L = +5%L / -0 | () [] | |
| NOCUMENT RTY OF CORPORATION. SERVED. | DESIGN IN THIS DOCUMENT IS THE PROPERTY OF FAIRVIEW MICROWAVE CORPORATION ALL RIGHTS RESERVED. | L ≤ 12 [305] = +1 [25] / -0 12 [305] < L ≤ 60 [1524] = +2 [51] / -0 [1524] < L ≤ 120 [3048] = +4 [102] / -0 | L ≤ 12 [305] = +1 [25] / -0 12 [305] < L ≤ 60 [1524] = +2 [51] / -0 60 [1524] < L ≤ 120 [3048] = +4 [102] / -0 | FRACTIONS ± 1/32 angles + 1° | [5.08] 2 [.51] 05[13] |
| ON AND | THE INFORMATION AND | L) TOLERANCES: | CABLE LENGTH (L) TOLERANCES | NCES: | TOLERANCES: |
| | 7-1-1-1 | | : | | 1 |

X = ±.2 [5.08] FRACTIONS XX = ±.02 [.51] ±1/32 XXX = ±.005[.13] ANGLES ± 1°

A

CAGE CODE 3FKR5